



Item No.	IP	L1	L2	Bφ	L3	Inner	W×H×D	g
XF-6 IP	6 IP	24	38	2.8	71	10	126×68×50	70
XF-7 IP	7 IP	24	38	2.8	71	10	126×68×50	70
XF-8 IP	8 IP	24	44.5	2.8	80.5	10	126×68×50	75
XF-9 IP	9 IP	24	44.5	2.8	80.5	10	126×68×50	75
XF-10 IP	10 IP	33	49	4.4	87	10	162×68×35	160
XF-15 IP	15 IP	33	49	4.4	87	10	162×68×35	165
XF-20 IP	20 IP	33	49	4.4	87	10	162×68×35	165

Tool Type: Torx Plus®  
 Handle Type: Flag Type  
 Measurement Type: Torx Plus®  
 Additional Information: Plastic Handle  
 Surface Treatment: Black Parkalized