



Item No.	IP	L1	L2	B	L3	Inner	W×H×D	g
XT-15 IP	15 IP	92	92	4	119	10	156×106×67	465
XT-20 IP	20 IP	92	92	4	119	10	156×106×67	465
XT-25 IP	25 IP	92	105	6.35	132	10	156×106×67	700
XT-27 IP	27 IP	92	105	6.35	132	10	156×106×67	700
XT-30 IP	30 IP	119	137	8	171	10	188×158×85	1,385
XT-40 IP	40 IP	119	137	8	171	10	188×158×85	1,385

Tool Type: Torx Plus®

Handle Type: T-Handle

Measurement Type: Torx Plus®

Additional Information: Plastic Handle