



## Oscillating Parabolic Heater, 1000W MODEL HTR70



- Safety tip over switch
- Safety overheat protection system
- 2 heat settings
- 70 degree oscillation
- Instant quiet heat
- Can help reduce heating bills
- Stay cool housing
- Carry handle



Save These Instructions

### INTENDED USE:

This product is intended for indoor residential and office use only, not for industrial or other commercial application. Use only with electrical wiring that is in good working order and that meets applicable codes and ordinances. This heater must be plugged in to a 120V AC, 15 Amp, (or larger) circuit. Do not plug anything additional into the same circuit. If you have any questions whether your wiring is adequate, consult a qualified electrician. Risk of fire, overheating, malfunction, property damage, injury or even death may result if not adhered to.

Use your heater only with a working smoke detector located in the vicinity of your heater.

While using your heater, you should follow the IMPORTANT INSTRUCTIONS listed below. As part of those instructions, we have used the word **"WARNING"** to indicate the level of hazard: **WARNING** indicates a hazard which, if not avoided, could result in injury or death.

## IMPORTANT INSTRUCTIONS

When using electrical appliances, basic precautions should always be followed to reduce the risk of fire, electric shock and injury to persons, including the following:

- Read all the instructions before using this heater/fan.
- This heater is hot when in use. To avoid burns, do not let bare skin touch hot surfaces. Use provided handle when moving this heater. Keep combustible materials, such as furniture, pillows, bedding, papers, clothes and curtains at least 3 feet (0.9 meters) from the front of the heater-fan and keep them away from the sides and rear.
- Do not use heater unattended. Use of extreme caution is necessary when any heater is used by or near children, invalids, disabled persons or pets.
- Do not operate the heater with a damaged power cord or after the heater malfunctions, has been dropped or damaged in any manner. Return heater to authorized service facility for examination, electrical or mechanical adjustment or repair.
- Do not use heater outdoors.
- Use your heater only in dry environments. This heater is not intended for use in a bathroom, laundry area, or similar locations, or near sinks, washing machines, swimming pools or other sources of water. Never locate heater where it may fall into a bathtub or other water container. Do not use in damp environments such as flooded basements.
- Do not place the heater on a small, unlevel, uneven or any surface which might allow heater to tip or fall.
- For proper operation, heater should be placed on a smooth, non-combustible surface. Do not place on rugs, carpet, vinyl flooring or other plastic surfaces. Not for use outdoors or in wet areas.
- This heater is not designed as a primary heat source.
- Always plug heaters directly into a wall outlet/receptacle. Never use with an extension cord or relocatable power tap (outlet/power strip). Always unplug heater when not in use.
- Do not run power cord under carpeting. Do not cover cord with throw rugs, runners or similar coverings. Arrange cord away from traffic area where it will not be tripped over.
- To disconnect heater, turn controls off then remove plug from outlet.
- Do not insert or allow foreign objects to enter any ventilation or exhaust opening as this may cause an electric shock or fire or damage the heater.
- To prevent a possible fire, do not block air intakes or exhaust in any manner. Do not use on soft surfaces like a bed, where openings may become blocked.
- A heater has hot and arcing or sparking parts inside. Do not use it in areas where gasoline, paint or flammable liquids are used or stored.
- Use this heater only as described in this manual. Any other use not recommended by the manufacturer may cause fire, electric shock or injury to persons or property.

### WARNING: SHOCK HAZARD

Use your heater only in dry environments. This heater is not intended for use in a bathroom, laundry area, or similar locations, or near sinks, washing machines, swimming pools or other sources of water. Never locate heater where it may fall into a bathtub or other water container. Do not use heater outdoors. Do not use in damp environments such as flooded basements.

### WARNING: HOT SURFACES

Do not touch body of heater when in use. This heater is hot when in use, to avoid burns, do not let bare skin touch hot surfaces. If provided, use handles when moving this heater.

### WARNING: FIRE HAZARD

Heater has hot and arcing or sparking parts inside. Do not use near combustible materials or flammable gases or sources of heat. DO NOT USE in areas where gasoline, paint or flammable materials are used or stored. Keep combustible materials such as furniture, pillows, bedding, papers, clothes and curtains at least 3 feet (0.9 m) from the front of the heater and keep them away from the sides and rear. To prevent a possible fire, do not block air intakes or exhaust in any manner. Do not use on soft surfaces, like a bed, where openings may become blocked. Do not place the heater near a bed because objects such as pillows or blankets can fall off the bed and be ignited by the heater. Do not insert or allow foreign objects to enter any ventilation or exhaust opening as this may cause an electric shock, fire, or damage the heater.

### WARNING: ELECTRICAL SHOCK HAZARD

Do not use with damaged cord or plug. Use with adequate electrical system that is up to code.

The supply cord has a polarized plug. As a safety feature this plug will fit in a polarized outlet only one way. To prevent electric shock, match wide blade of plug to wide slot, fully insert plug. If the plug does not fit contact a qualified electrician.

Do not operate any heater with a damaged cord or plug or after heater malfunctions, has been dropped or damaged in any manner. Do not operate heater with a broken heating element or ceramic cone or any visual imperfections. For repairs covered under warranty, see warranty statement.

### PET OWNERS NOTE:

The health of birds and some small pets are extremely sensitive to the fumes given off during the initial use of many appliances. Although these fumes are not harmful to humans, it is recommended that this heater not be used around birds and small pets during its initial use until the manufacturing corrosion coatings burn off.

## SAVE THESE INSTRUCTIONS

Page 2

### USAGE:

**HEATER OPERATION:** Always operate the heater in the upright position following all instructions and commendations listed in this manual. **HEATER LOCATION:** Place the heater in the area of the room that is coldest. **HEATER CONNECTION:** Plug heater directly into 120 Volt A.C., 60 Hz wall outlet. Be sure plug fits tightly in outlet. A loose connection may cause overheating and damage to the plug or heater. **NOTE:** The heater draws 8.33 amps during operation. To prevent overloading a circuit, do not plug the heater into a circuit that is servicing other electrical needs.

**TURNING HEATER ON:** To start the heater, turn the POWER SWITCH (left knob) from the off position to the LOW (700 Watt) or HIGH (1000 WATT) position. (During the heaters initial use, you may experience a slight odor or smoking. This is the result of the heating element lubrication "burning off". This is normal and will go away after a few minutes of use.)



**OPERATION SWITCH:** This heater has two heat settings: LOW (700 Watts) and HIGH (1000 Watts). Use the HIGH setting to raise the room temperature quickly. When the desired temperature is reached use the LOW setting to maintain temperature. It is usually sufficient to maintain a comfortable temperature.


**TILT FEATURE:** Your heater can tilt for adjusting the direction of heat. To adjust the angle, loosen tilt adjustment knob and move angle of the heater to desired position. Tighten tilt adjustment knob to hold heater in position. Do not force the heater in either direction beyond its guides.

**TURNING OFF:** Turn the selector switch to the OFF position before unplugging or plugging in the heater. Heater should be unplugged when not in use.

**OSCILLATION CONTROL:** You can control the Oscillation feature on the Heater by rotating the Oscillation Control (OSC) switch located on the control panel of the heater.

### USERS NOTE:

The coils in the center of the dish are very hot. It is normal that not all coils are glowing during use. The non-glowing elements are functioning properly and generating heat.



### IMPORTANT SAFETY FEATURES

The heater is equipped with an automatic overheat protection device and an automatic tip-over sensor located under the base of the heater. If the heater grille is obstructed, the automatic overheat device will turn the heater off. If the heater is tipped over, the automatic tip-over switch will turn off the heater. If either safety sensor is activated, make sure the heater is on a level surface and clear of all obstacles. Unplug the heater and allow it to cool down before restarting. After cooling down and obstacles have been removed.

### CARE AND MAINTENANCE

**CLEANING:** CAUTION-Before cleaning the heater be sure to disconnect power cord and allow the heater to cool completely. This heater should be cleaned at least once a year to maintain proper performance. Clean the outside surface with a clean damp cloth. Do not use harsh chemical or abrasive cleaners. DO NOT IMMERSE THE HEATER IN WATER. Allow heater to dry completely before use.

**REPAIR:** DO NOT OPERATE THE HEATER WITHOUT THE GRILLE IN PLACE. DO NOT USE THE HEATER IF IT HAS MALFUNCTIONED OR BECOME DAMAGED IN ANY WAY.

**STORAGE:** Keep original carton for storage of the heater. Coil and tie the power cord to avoid damage during storage.

### LIMITED WARRANTY

A limited warranty is extended to the original purchaser of this heater and Proaira warrants against malfunction due to defects in material or workmanship for a period of one (1) year from the original date of purchase (the "Warranty Period"). If such a defect is discovered within the Warranty Period, Proaira will, at its option, repair or replace the product at no cost after a thorough review of the defect. Replacements outside of the Warranty Period will require a fee to cover materials, labor, handling and shipping.

This limited warranty does not apply to defects resulting from misuse or use contrary to the owner's manual and safety guidelines, damage caused by an improper voltage, damage caused by use outdoors, modification, alteration, repair or service of the product by a third party, mishandling, improper maintenance, commercial use of the product, damages which occur in shipment or are attributed to acts of God.

This limited warranty does not imply or assume any responsibility for consequential damages that may result from the use, misuse, or the lack of routine maintenance of this heating appliance. This limited warranty does not cover claims which do not involve defective material or workmanship. FAILURE TO PERFORM GENERAL MAINTENANCE WILL VOID THIS LIMITED WARRANTY.

THIS LIMITED WARRANTY IS GIVEN TO THE ORIGINAL PURCHASER IN LIEU OF ALL OTHER WARRANTIES, EXPRESS OR IMPLIED, INCLUDING BUT NOT LIMITED TO THE WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PRODUCT. THE REMEDY PROVIDED IN THIS LIMITED WARRANTY IS EXCLUSIVE AND IS GRANTED IN LIEU OF ALL OTHER REMEDIES. IN NO EVENT WILL PROAIRA BE LIABLE FOR INCIDENTAL OR CONSEQUENTIAL DAMAGES.

Some states do not allow the exclusion or limitation of incidental or consequential damages or allow limitations on how long an implied warranty lasts, so the above limitations or exclusions may not apply to you. This limited warranty gives you specific legal rights, and you may have other rights that vary from state to state.

For full details, please contact Proaira Customer Service with proof of purchase.

Customer Service:  
Phone: (877) 599-4747  
Fax: (877) 600-4747  
Email: info@proaira.com

Manufactured for:  
Proaira  
1060 Commerce Ave.  
Union, NJ 07083 USA  
(877) 599-4747  
www.proaira.com

Page 3

Page 4