

Extreme Hold Mounting Tape



FEROCIOUSLY STRONG, DOUBLE SIDED MOUNTING TAPE



TYPICAL APPLICATIONS

- Indoor/Outdoor mounting tape works on a variety of surfaces including metal, glass, wood, concrete, brick, tile, and ceramic
- Offers an easy alternative to nails, screws, staples or glue
- designed specifically to hold longer and stronger for projects both big and small

PRODUCT FEATURES

- Permanent, double-sided mounting tape specifically designed to withstand high temperatures.
- All weather mounting tape withstands extreme temperature ranges
- Extreme hold during indoor/outdoor use and is weather resistant for year-long durability

CONSTRUCTION

Overall Grade/Function: Super Tough
Backing: Foam with Polyethylene Release Liner
Adhesive: Double Sided Acrylic Based

STANDARD WIDTH(S)

1 in

STANDARD LENGTH(S)

60 yd

STORAGE AND USAGE CONDITIONS

Tape should be stored in its original packaging in a cool, dry area away from direct sunlight and should be used within 12 months of date of shipment. Surfaces to which tape is applied should be clean, dry and free of grease, oil or other contaminants.

COLOR(S)



PHYSICAL PROPERTIES

	STANDARD	METRIC
Tensile Strength	85 lb/in ² width	58.6 N/cm ²
Adhesion to Steel	23 lb/in width	40.3 N/cm
Thickness	47 mils	1.2 mm
Service Temperature Range	-40 F to 200 F	-40 C to 93 C
Application Temperature	50 F to 200 F	10 C to 38 C

Physical and performance characteristics shown above are obtained from tests recommended by PSTC, ASTM, government agencies or Shurtape Technologies, LLC, Quality Assurance and Technical Service departments and do not represent a guarantee of product performance. Individual rolls may vary slightly from these averages. The user should determine whether the product is fit for a particular purpose and is suitable for the user's method of application before use.



Shurtape

TECHNOLOGIES