

### Specifications:

<b>Print Technology</b>	Digital Color LED
<b>LCD Display (type/size)</b>	1-line mono (backlit)
<b>Paper Size (maximum)</b>	Up to 8.5" x 14" (legal)
<b>Print Speed (maximum)</b>	Black: up to 19ppm Color: up to 19ppm
<b>Time to First Page<sup>▼</sup></b>	Black: < 15.5 seconds Color: < 15.5 seconds
<b>Print Resolution (maximum)</b>	Up to 600 x 2400 dpi
<b>Processor</b>	800MHz
<b>Emulations</b>	PCL®6, GDI, BR-Script3*
<b>Paper Input Capacity (maximum)<sup>∞</sup></b>	Up to 250-sheet paper tray, single-sheet manual feed slot
<b>Media Types</b>	Plain paper, recycled paper, bond, envelopes, labels & glossy paper
<b>Media Weights</b>	Paper Tray: 16-43 lbs. (bond) Manual Feed Slot: 16-43 lbs. (bond)
<b>Print Driver Settings</b>	Toner Save, N-Up, Watermark <sup>‡</sup> , Poster <sup>‡</sup> , Header-Footer <sup>‡</sup> , Secure Print
<b>Memory (std. / max.)</b>	256MB / 256MB
<b>Standard Interfaces</b>	Wireless 802.11b/g/n, Hi-Speed USB 2.0
<b>Operating Systems Compatibility</b>	Windows 7, 8, 8.1, 10 / Server 2008, Server 2008 R2, Server 2012, Server 2012 R2, Server 2016 macOS v10.11.6, 10.12.x, 10.13.x (Download only)
<b>Mobile Device Compatibility<sup>□</sup></b>	AirPrint®, Google Cloud Print™, Brother iPrint&Scan (free downloadable app), Mopria, and Wi-Fi Direct®
<b>Maximum Monthly Duty Cycle<sup>Ⓣ</sup></b>	Up to 30,000 pages
<b>Recommended Monthly Volume<sup>*</sup></b>	Up to 1,500 pages
<b>Warranty</b>	1-year Limited Warranty
<b>ENERGY STAR® Qualified</b>	Yes

▼ From Ready mode and standard tray.

∞ Maximum capacity based on using 20 lb. paper.

‡ Windows Only.

‡ Additional purchase required.

Ⓣ Maximum number of printed pages per month can be used to compare designed durability between like Brother products. For maximum printer life, it is best to choose a printer with a duty cycle that far exceeds your print requirements.

□ Requires connection to a wireless network.

\* The recommended range of monthly printed pages to achieve the best possible performance and printer life. Printers are intended to handle occasional usage beyond this range with little or no effect. Consistently printing above the recommended print volume, however, may adversely affect the print quality or life of the machine. It is always best to choose a printer with an appropriate recommended print volume to allow for any anticipated increase in printing needs.

^ Approximate yield in accordance with ISO/IEC 19798 (Letter/A4).

\*\* Drum yield is approximate and may vary based on type of use.

\*\* Approximate yield based on A4 or Letter size single-sided pages.

\* PostScript®3™ compatible.



### Working with you for a better environment

At Brother, our green initiative is simple. We strive to take responsibility, act respectfully and try to make a positive difference to help build a society where sustainable development can be achieved. We call this approach Brother Earth. [www.brotherearth.com](http://www.brotherearth.com)

### Supplies\*:



TN223BK	Standard Yield Black Toner Cartridge (1,400 pgs) <sup>^</sup>
TN223C	Standard Yield Cyan Toner Cartridge (1,300 pgs) <sup>^</sup>
TN223M	Standard Yield Magenta Toner Cartridge (1,300 pgs) <sup>^</sup>
TN223Y	Standard Yield Yellow Toner Cartridge (1,300 pgs) <sup>^</sup>
TN227BK	High Yield Black Toner Cartridge (3,000 pgs) <sup>^</sup>
TN227C	High Yield Cyan Toner Cartridge (2,300 pgs) <sup>^</sup>
TN227M	High Yield Magenta Toner Cartridge (2,300 pgs) <sup>^</sup>
TN227Y	High Yield Yellow Toner Cartridge (2,300 pgs) <sup>^</sup>
DR223CL	Drum Unit Set (18,000 pgs) <sup>**</sup>
BU223CL	Belt Unit (50,000 pgs A4/Letter)
WT223CL	Waste Toner Box (50,000 pgs) <sup>**</sup>
BP60MPLTR	Multi Purpose Paper (Letter, 500 sheets)

### Setup Information:

<b>UPC Code</b>	012502651741
<b>Unit Dimensions</b>	16.1" W x 18.1" D x 9.9" H
<b>Unit Weight</b>	37.8 lbs.
<b>Carton Dimensions</b>	23.2" W x 20.2" D x 14.6" H
<b>Carton Weight</b>	45.5 lbs.
<b>Pallet Quantity</b>	12
<b>Pallet Tiers</b>	3
<b>Pallet Quantity per Tier</b>	4
<b>Pallet Size</b>	48" x 40"
<b>Pallet + Cartons Height</b>	48.9"
<b>Pallet + Carton Weight</b>	576.0 lbs
<b>Country of Origin</b>	Vietnam
<b>Tariff / Harmonized Code</b>	8443.32.1090

### Carton Contents:

Brother HL-L3210CW
Starter Black Toner Cartridge (1,000 pages) <sup>^</sup>
Starter Cyan Toner Cartridge (1,000 pages) <sup>^</sup>
Starter Yellow Toner Cartridge (1,000 pages) <sup>^</sup>
Starter Magenta Toner Cartridge (1,000 pages) <sup>^</sup>
DR223CL Drum Unit Set (18,000 pgs) <sup>**</sup>
CD-ROM Includes Printer Drivers
Quick Set-Up Guide

### Scannable Barcode:

