

Specifications:

Print Technology	4-cartridge Color Inkjet
LCD Display (type/size)	1.8" Color Display
Paper Size (maximum)	Paper Tray: Up to 8.5" x 14" (legal size)
Print Speed (maximum)¹	Black (ISO/IEC 24734): Up to 17ppm Color (ISO/IEC 24734): Up to 9.5ppm
FPOT (First Print Out Time)²	Black: Approx. 6.9 Seconds Color: Approx. 10.5 Seconds
Print Resolution (maximum)³	Windows: Up to 6000 x 1200 dpi Mac [®] : Up to 3600 x 1200 dpi
Duplex Printing Capability	Yes (up to 8.5"x11")
Borderless Printing Capability⁴	Yes (Letter, 4x6, 5x8, 3.5x5, 5x7, and A4)
Paper Input Capacity (maximum)	Up to 150 sheets
Auto Document Feeder	Yes (up to 20-sheets)
Standard Interfaces⁵	Wireless (802.11 b/g/n), Wi-Fi Direct [®] , Hi-speed USB 2.0
Copy Speed (maximum)⁶	Black (ISO/IEC 24735): Up to 11.5ppm Color (ISO/IEC 24735): Up to 4.0ppm
Copy Resolution (maximum)³	Up to 600 x 1200 dpi
Copy Reduction/Enlargement	25% - 400% in 1% increments
Copy Options	Stack, Sort, N-in-1, ID Copy, Fit to Page, Base Color Removal
Scanner Type	Color Flatbed (CIS)
Document Glass Size	Letter Size 8.5" x 11.7"
Scan / Copy Size (maximum)	Letter (8.5" x 11")
Scan Resolution (maximum)³	Optical: 2400 x 1200 dpi (Flatbed) 600 x 1200 (ADF) Interpolated: 19200 x 19200 dpi
Fax Modem	14.4 Kbps
Fax Page Memory (maximum)⁷	Up to 170 pages
Speed Dial Locations	40
PC Fax Capability⁸	Yes (black & white only)
Web Connectivity⁹	GOOGLE DRIVE™, EVERNOTE®, DROPBOX, BOX, ONEDRIVE, ONENOTE, BROTHER CLOUD APPS
Brother Cloud Apps¹⁰	Scan to Office, Scan to Searchable PDF, Easy Scan to E-mail
Operating Systems Compatibility¹¹	PC: Windows 7 SP1 / 8.1 / 10 Home / 10 Pro / 10 Education / 10 Enterprise Windows 2008 R2 / 2012 / 2012 R2 / 2016 / 2019 Windows Server 2008 / MAC [®] : OS v10.14.6, 10.15.x, 11
Mobile Device Compatibility¹²	AirPrint [®] , Mopria [®] , Wi-Fi Direct [®] , and Brother Mobile Connect
Maximum Monthly Duty Cycle¹³	Up to 2,500 pages
Recommended Monthly Volume¹⁴	Up to 1,000 pages
Warranty	1-year Limited Warranty
ENERGY STAR[®] Qualified	Yes

Supplies & Accessories¹⁵:

LC401XLBK	High Yield Black Ink Cartridge (approx. 500 pages) ¹⁶
LC401XLC	High Yield Cyan Ink Cartridge (approx. 500 pages) ¹⁶
LC401XLM	High Yield Magenta Ink Cartridge (approx. 500 pages) ¹⁶
LC401XLY	High Yield Yellow Ink Cartridge (approx. 500 pages) ¹⁶
LC401BK	Standard Yield Black Ink Cartridge (approx. 200 pages) ¹⁶
LC401C	Standard Yield Cyan Ink Cartridge (approx. 200 pages) ¹⁶
LC401M	Standard Yield Magenta Ink Cartridge (approx. 200 pages) ¹⁶
LC401Y	Standard Yield Yellow Ink Cartridge (approx. 200 pages) ¹⁶
BP71GLTR	Innobella Letter-size Glossy Inkjet Paper (20 sheets)
BP71GP20	Innobella 4" x 6" Glossy Photo Paper (20 sheets)
BP60MPLTR	Innobella Letter-size Multi-Purpose Paper (500 sheets)

Carton Contents:

Brother MFC-J1010dw
Black, Cyan, Magenta, Yellow Starter Ink Cartridges
Quick Setup Guide
Product Safety Guide
Reference Guide
Warranty Card
Telephone Line Cord

Setup Information:

UPC Code	012502663959
Unit Dimensions (WxDxH)	15.7" x 13.5" x 6.8"
Unit Weight	16.4 lbs
Carton Dimensions (WxDxH)	18.8" x 9.8" x 18.0"
Carton Weight	21.6 lbs
Pallet Quantity	20
Pallet Tiers	2
Pallet Quantity per Tier	10
Pallet Size	48" x 40"
Pallet + Cartons Height	41"
Pallet + Carton Weight	462.5 lbs
Country of Origin	Philippines
Tariff / Harmonized Code	8443.31.0000

Scannable Barcode:



1 ISO print speed based on ISO/IEC 24734 (after first set of ISO test pages). For more details, visit www.brother-usa.com.

2 From ready mode and standard tray.

3 Resolutions are listed by vertical by horizontal dpi.

4 Borderless not available on duplex. Minimum default margins .12" on all sides.

5 Cables not included.

6 ISO copy speed is based on ISO/IEC 24735. For more details, visit www.brother-usa.com.

7 Black and white only. Based on ITU-test 1 Chart No.1 at standard resolution with MMR compression.

8 PC-Fax Send Only for Mac[®] users.

9 Requires internet connection and an account with desired service.

10 Requires connection to a wireless network. Requires internet connection.

11 See system requirements on www.brother.com

12 Requires connection to a wireless network.

13 Maximum number of printed pages per month and can be used to compare designed durability between like Brother products. For maximum printer life, it is best to choose a printer with a duty cycle that far exceeds your print requirements.

14 The recommended range of monthly printed pages to achieve the best possible performance and printer life. Printers are intended to handle occasional usage beyond the range with little or no effect. Consistently printing above the recommended print volume, however, may adversely affect the print quality or life of the machine. It is always best to choose a printer with an appropriate recommended print volume to allow for any anticipated increase in printing needs.

15 Additional purchase required.

16 Approximate page yields in accordance with ISO 24711. For more page yield information see www.brother.com/pageyield.