



PIXMA G3200

Setup Sheet

Wireless MegaTank All-In-One Printer

Version 1.1



RETHINK THE WAY YOU PRINT WITH CONTINUOUS INK

Introducing the Canon PIXMA G3200 Wireless MegaTank All-In-One Printer—the perfect printer for people who print a lot and copy a lot. That’s because its MegaTank ink reservoir system allows it to print up to 6,000 crisp black pages / 7,000 magnificent color pages¹ from one set of replacement inks bottles. Do the math and that’s more than 30 times as many prints as you can get from conventional ink cartridge sets!² Quality is quite impressive too, because hybrid ink formulations produce deeper blacks and more vibrant colors. Plus, the PIXMA G3200 printer connects to your favorite mobile devices wirelessly³ or through the cloud⁴, so it’s always ready to go, even when you’re on the go. The Canon PIXMA G3200 Wireless MegaTank All-In-One Printer. Mega printing performance is here!

CORE FEATURES



Integrated Ink Tanks

Conveniently view and refill ink with **INTERGRATED INK TANKS**.



Sharp Black Text

Print detailed documents with **SHARP BLACK TEXT** from the pigment black ink.



30 TIMES the amount of ink - compared to standard ink cartridge sets.²



With the **CANON PRINT APP**⁵ conveniently print from your favorite mobile devices.



GOOGLE CLOUD PRINT⁶ makes it easy to print from your **Android**TM phone and tablet.



Borderless Printing

Print beautiful **BORDERLESS PHOTOS**⁷ effortlessly.



Print from any room in the house with **BUILT IN WI-FI**⁸.



PIXMA G3200

Wireless MegaTank All-In-One Printer

TECHNICAL SPECIFICATIONS

PRINT

Print Features Auto Photo Fix II, Borderless Printing⁷, Business Card Printing, Canon PRINT app⁵, Document Printing, Easy PhotoPrint+⁸, Full HD Movie Print⁹, Google Cloud Print⁹, High Page Yield, Image Cropping, My Image Garden¹⁰, Photo Printing, PIXMA Cloud Link⁴, Quiet Mode, Red-Eye Correction, Special Filters, Square Media Printing Support, Wireless Printing³

Print Speed¹¹ 4" x 6" Photo: Approx. 60 seconds (Borderless)
ESAT (Black): Approx. 8.8 ipm
ESAT (Color): Approx. 5.0 ipm

Number of Nozzles Color: 1,152 / Pigment Black: 320 / Total: **1,472**

Print Resolution¹² Up to 4800 x 1200 dpi

Paper Sizes 4" x 6", 5" x 5" Square, 5" x 7", 8" x 10", Letter, Legal, U.S. #10 Envelopes

Media Compatibility **Plain:** Plain Paper, Canon High Resolution Paper; **Glossy:** Photo Paper Plus Glossy II, Photo Paper Glossy; **Semi-Gloss:** Photo Paper Plus Semi-Gloss, Photo Paper Pro Luster; **Matte:** Matte Photo Paper **Other:** U.S. #10 Envelopes

Paper Capacity Rear Paper Tray: 100 Sheets of Plain Paper **OR**
Photo Paper: 20 Sheets of 4" x 6" / 10 Sheets of 5" x 7"

COPY

Copy Features Standard Copy

Copy Speed¹¹ FCOT (Color): Approx. 24 seconds

SCAN

Scan Features Auto Scan Mode¹³, Document Removal Reminder, Network Scan, Wireless Scanning³

Scanner Type Flatbed

Scanning Method Contact Image Sensor (CIS)

Scanning Resolution¹⁴ 600 x 1200 dpi (Optical)
19,200 x 19,200 dpi (Interpolated)

Maximum Color Scanning Bit Depth 48-bit Internal
24-bit External

Maximum Document Size Flatbed: 8.5" x 11.7"

INK INFORMATION

INK TYPE

GI-290 BK: Pigment Based Ink
GI-290 C/M/Y: Dye Based Inks

INK BOTTLES & FILL VOLUME

GI-290 BK: 135.0 ml
GI-290 C: 70.0 ml
GI-290 M: 70.0 ml
GI-290 Y: 70.0 ml

HIGH PAGE YIELD

Up to **6,000** (Black & White) / **7,000** (Color) Pages¹

GENERAL

STANDARD INTERFACE

Hi-Speed USB
Wireless LAN (IEEE 802.11b/g/n)³

GENERAL FEATURES

4-Color MegaTank Refillable Ink System, Auto Power On/Off, Canon PRINT app³, PIXMA Cloud Link¹¹

OS COMPATIBILITY

Windows:¹⁵ Windows[®] 10, Windows 8, Windows 8.1, Windows 7 SP1, Windows Vista[®] SP2, Windows XP SP3 (32-bit only)

Mac:¹⁶ Mac OS[®] X v10.8.5 – macOS v10.12 (Sierra)

Mobile Operating Systems:¹⁷ iOS[®], Android, Windows 10 Mobile, Windows RT¹⁸, and Amazon Fire devices¹⁹

SOFTWARE (WINDOWS¹⁵/MAC¹⁶)

PIXMA G3200 MegaTank All-In-One Printer Driver

Scan Utility

Master Setup

My Image Garden¹⁰

Full HD Movie Print⁹, Special Filters, Image Correction/Enhance, and scanning are accessed through My Image Garden

Quick Menu

WARRANTY²⁰

1-Year limited warranty with InstantExchange Program. 1-Year toll-free U.S.-based technical phone support.

BOX CONTENTS

PIXMA G3200 Wireless MegaTank All-In-One Printer
Setup CD-ROM

Full Set of Ink Bottles (BK,C,M,Y)

Black Print Head

Color Print Head

Power Cord



PIXMA G3200

Wireless MegaTank All-In-One Printer

ORDERING INFORMATION

MODEL NUMBER	DESCRIPTION	ITEM NUMBER	UPC CODE
 PIXMA G3200	Wireless MegaTank All-In-One Printer	0630C002[AA]	 0 13803 28115 6

COMPATIBLE INK BOTTLES

 290 BK	GI-290 BK	Pigment Black Ink Bottle	1595C001[AA]	 0 13803 28078 4
 290 C	GI-290 C	Cyan Ink Bottle	1596C001[AA]	 0 13803 28079 1
 290 M	GI-290 M	Magenta Ink Bottle	1597C001[AA]	 0 13803 28080 7
 290 Y	GI-290 Y	Yellow Ink Bottle	1598C001[AA]	 0 13803 28081 4

PALLET INFORMATION

Number of Boxes per Pallet	16
Number of Boxes per Layer	4
Number of Layers per Pallet	4
Dimensions (Pallet and Boxes)	48.0" (W) x 40.0" (D) x 45.1" (H)
Dimensions without Pallet	41.8" (W) x 38.2" (D) x 39.6" (H)
Loaded Pallet Weight	374.8 lbs.

ORIGIN

Country of Origin	Vietnam
Tariff Number	8443310000

PRINTER INFORMATION

Printer Dimensions	17.6" (W) x 13.0" (D) x 6.5" (H)
Printer Weight	12.7 lbs.

BOX INFORMATION

Box Dimensions ²¹	20.9" (W) x 19.1" (D) x 9.9" (H)
Box Weight	20.3 lbs.

DATE

Availability	Late December 2016
--------------	--------------------

SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE. ALL VIEWSCREEN AND OUTPUT IMAGES ARE SIMULATED.

- Page yield of included ink bottles used for initial setup is lower than the replacement ink bottles, as a certain amount of ink is consumed to fill into the print head during the setup (charging the print head initially). Page yield is the estimated value based on Canon individual test method using the ISO/IEC 24712 chart and continuous printing simulation with the replacement ink bottles after initial setup. Page yield of color inks is an average yield of cyan, magenta and yellow inks combined. Page yield varies significantly depending on content printed and other factors. Up to 6,000 (black) / 7,000 (color) printed page yields are approximate, based off document pages printed.
- 30 ink cartridge sets is based on print yield of the included black and color ink bottles as compared to the following standard-capacity cartridge sets: PG-245 Black Ink Cartridge and CL-246 Color Ink Cartridge as of August 2016.
- Wireless printing and scanning requires a working network with wireless 802.11b/g or n capability. Wireless performance may vary based on terrain and distance between the printer and wireless network clients.
- Requires an Internet Connection.
- Requires an Internet connection and the Canon PRINT Inkjet/SELPHY app, available for free on the App Store and at Google Play. Compatible with iPad, iPhone 3GS or later, and iPod touch 3rd generation or later devices running iOS 7.0 or later, and Android™ mobile devices running Android 2.3.3 or later. Your device must be connected to the same working network with wireless 802.11 b/g/n capability as your printer. Requires a compatible social media account and is subject to that social media account's Terms of Service. Certain exceptions may apply.
- Requires an Internet connection and Google account. Subject to Google Terms of Service. Certain exceptions may apply.
- Paper types NOT supported for borderless printing are as follows: Envelope, High Resolution Paper, T-Shirt Transfer, Photo Stickers.
- Works edited by using this application cannot be displayed, edited, or printed without this application. Compatible with Android device of 7 inches or more using Chrome (latest version compatible with your current version of Android™ OS), iOS Devices of 7 inches or more using Safari 5.1 or later, Windows PC (excluding RT) using Internet Explorer 10 or later of Microsoft Modern UI version, Microsoft Internet Explorer 9 or later, Mozilla Firefox 31 or later, or Google Chrome version 36 or later, and with Mac OS X 10.6.8 or later using Safari 5.1 or later.
- "Full HD Movie Print" is available from "MOV" and "MP4" movie files created by select Canon EOS Digital SLRs, PowerShot, and VIXIA digital cameras and camcorders. Requires PC or Mac with Intel® processor and Canon ZoomBrowser EX 6.5 or later or Canon ImageBrowser 6.5 or later for "MOV" files, or Canon ImageBrowser EX 1.0 or later for "MP4" files. Print quality is determined by the video resolution. Function does not upscale video resolution.
- To install using Windows® OS, .NET Framework 4 is required. Compatible still image formats are PDF (created using Canon PDF Creator only), JPEG (Exif), TIFF, and PNG. Compatible video formats are MOV (from select Canon digital cameras only) and MP4 (from select Canon digital camcorders only).
- Document print speeds are the averages of ESAT in Office Category Test for the default simplex mode, ISO/IEC 24734. Photo print speed is based on the default setting using ISO/JIS-SCID N2 on Photo Paper Plus Glossy II and does not take into account data processing time on host computer. Print speed may vary depending on system configuration, interface, software, document complexity, print mode, page coverage, type of paper used etc. Copy speeds are the average of sFCOT and sESAT, ISO/IEC 29183. Copy speed may vary depending on document complexity, copy mode, page coverage, type of paper used etc. and does not take into account warming up time. See www.usa.canon.com/ipm for additional details.
- Resolution may vary based on printer driver setting. Color ink droplets can be placed with a horizontal pitch of 1/4800 inch at minimum.
- For network users, Auto Scan Mode is only available when scanning at a computer using My Image Garden software and selecting the I-click feature then "Save to PC".
- Optical resolution is a measure of maximum hardware sampling resolution, based on ISO 14473 standard.
- Operation can only be guaranteed on a PC with pre-installed Windows 10, Windows 8.1, Windows 8, Windows 7, Vista SP2 or Windows XP SP3 (32 bit only).
- Internet Connection required during software installation. For full compatibility macOS v10.12.1 or later is recommended.
- Some functions may not be available with these Operating Systems. Please refer to manual or our website for details.
- Requires a Windows RT compatible device and the Canon Easy-PhotoPrint app for Windows RT available for free in the Windows Store.
- Requires "Canon Print Plug-in" available for free from the Amazon Appstore and an Amazon Fire Phone, Amazon Kindle Fire HD6 or HDX7 device or later running Fire OS 4.0 or later.
- Warranty programs are subject to certain conditions and restrictions. See www.usa.canon.com/support for details.
- Product box dimensions measured in horizontal box configuration.



©2017 Canon U.S.A., Inc. Canon and PIXMA are registered trademarks of Canon Inc. in the U.S. and may be registered trademarks or trademarks in other countries. Microsoft, Windows, the Windows logo and Internet Explorer are trademarks or registered trademarks of the Microsoft group of companies in the U.S. and other countries. Apple, iPad, iPhone, iPod touch and Time Capsule are registered trademarks of Apple Inc. Android and Google Play are trademarks of Google Inc. The USB-IF logo is a trademark of Universal Serial Bus Implementers Forum, Inc. Wi-Fi is a registered trademark of the Wi-Fi Alliance. The 'Wi-Fi CERTIFIED' logo is a certification mark of the Wi-Fi Alliance. The Wi-Fi Protected Setup Mark is a mark of the Wi-Fi Alliance. All other product and brand names are trademarks of their respective owners. As an ENERGY STAR® partner, Canon U.S.A., Inc. has determined that this product meets the ENERGY STAR® guidelines for energy efficiency.

