



Oxivir® Five 16 Concentrate

57

One-Step Disinfectant Cleaner

Dilutable, one-step disinfectant cleaner formulated with proprietary Hydrogen Peroxide technology.

Features & Benefits

- One-step disinfectant cleaner powered by Accelerated Hydrogen Peroxide® (AHP®) technology
- Disinfects in just 5 minutes with no VOCs, no added fragrance and no NPEs
- Effective against Human Immunodeficiency Virus (HIV-1 (AIDS Virus)), Hepatitis C Virus, Poliovirus, Avian Influenza A, *Pseudomonas aeruginosa*, *Staphylococcus aureus*, *Methicillin-resistant Staphylococcus aureus (MRSA)*, *Salmonella enterica*, and *Vancomycin-resistant Enterococcus faecium (VRE)*
- Kills Norovirus and Canine Parvovirus and is compatible with most hard, non-porous surfaces
- Environmentally responsible-active ingredient breaks down to oxygen and water after use

Applications

- Clean and disinfect high-touch surfaces in 5 minutes



* Note: not recommended for floors at disinfectant strength (1:16).





Oxivir® Five 16 Concentrate

One-Step Disinfectant Cleaner

Use Directions:*

- Spray surfaces and let solution remain on surface for a minimum of 5 minutes
- Air Dry, wipe surfaces to dry and remove any residue, or rinse with potable water as necessary
- Prepare a fresh solution if the solution becomes visibly dirty or diluted

Dilutable Disinfectant Cleaner

- 1:16 dilution – Virucidal, Bactericidal, and Fungicidal, including antibiotic resistant bacteria, in 5 minutes
- 1:128 dilution – Non-food contact sanitizer in 3 minutes or general purpose cleaning
- 1:256 dilution – Floor and general purpose cleaner

Note: Rinsing is not necessary unless floors are coated with finish or restorer.

All food contact surfaces must be rinsed with potable water. Do not use on glassware, utensils or dishes. Prior to first use on a particular surface, it is recommended to test in a small, discreet area if there is concern of incompatibility, or contact a Diversey representative.

* Not recommended for floors at dilution 1:16. Refer to product label for complete use instructions.

Technical data	Oxivir® Five 16 Concentrate
EPA Reg. No.	70627-58
Color	Colorless, liquid
pH	1.0 (Concentrate) 1.9 (Use Dilution 1:16)
Scent	Characteristic of ingredients
Shelf Life	3 Years

Product	Pack size	Dilution	Product code	
Oxivir® Five 16 Concentrate	4 x 1 gallon / 3.78 L Containers	1:16, 1:64, 1:128, 1:256	4963314	
Oxivir® Five 16 Concentrate	2 x 2.5 L / 84.5 oz. J-Fill® Bottles	1:16	4963331	
Oxivir® Five 16 Concentrate	2 x 1.5 L / 1.59 Qt. RTD® Units (Fill)	1:16, 1:64, 1:128, 1:256	4963357	
Oxivir® Five 16 Concentrate	2 x 1.4 L / 1.48 Qt. SmartDose™ Bottles	1:16 (Spray Bottle), 1:256 (Mop Bucket)	5019296	
Oxivir® Five 16 Concentrate	2 x 1.5 gallon / 5.67 L Command Center® Units	1:16, 1:64, 1:128, 1:256	5271361	
Oxivir® Five 16 Concentrate	12 x 32 oz. / 946 mL Empty Spray Bottles		D1222663	
Oxivir® Five 16 Concentrate	1 x 5 gallon Container	1:16, 1:64, 1:128, 1:256	101104070	

SmartDose™ Icons



Handling

Please make sure your employees read and understand the product label and Safety Data Sheet before using this product. The label contains directions for use; and both the label and SDS contain hazard warnings, precautionary statements and first aid procedures. SDS are available online at www.diversey.com or by calling 888.352.2249. Improper use or dilution may result in damage to surfaces and may result in health and physical hazards that match those of the concentrate.

AHP® and Design are trademarks of Diversey, Inc.

www.diversey.com

© 2020 Diversey, Inc. All Rights Reserved. PSS750 (20/153)