



Stride® Citrus

3

Neutral Cleaner

Stride® Citrus Neutral Cleaner is a non-alkaline formulation for everyday cleaning of floors and other hard services.

Features & Benefits

- Concentrated formulations deliver economical cleaning performance
- Low-foaming formula allows for less emptying of recovery tanks and increased productivity
- Neutral pH formulation that does not require rinsing and dries film-free
- Most SKUs meet the Green Seal® GS 37 standard and GreenGuard® indoor air quality certification

Applications

- For use as a daily and general cleaner
- Versatile formula that performs in a variety of application methods such as an autoscrubber, spray and wipe and mop and bucket





Stride® Citrus

Neutral Cleaner

Use instructions

- Dust mop or sweep floor.
- Dilute, dose or dispense product into spray bottle, mop bucket or autoscrubber using cold water.

Mop and Bucket Floor Cleaning

- Mop floors; no rinsing is necessary.
- Pick up excess cleaner with lightly wrung-out mop.

Automatic Scrubber Floor Cleaning

- Scrub with red pad daily.
- Double-scrub with green/blue pad before recoating or restoring. Trail mop machine turns, edges and low spots to pick-up cleaning solution left behind by machine.
- Floors will be slippery when wet.

Spray and Wipe Cleaning

- Spray, wipe and allow surface to dry.

Technical data	Stride® Citrus
Certifications	Green Seal®, GreenGuard®
Color/Form	Clear Orange Liquid
pH	6.5–7.0 (Concentrate, SC, HC) 6.9–7.3 (Use Dilution)
Scent	Citrus
Shelf Life	2 Years

Product	Pack size	Dilution	Product code	
Stride® Citrus	4 x 1 gallon / 3.78 L Containers - Concentrate	Mop Bucket: 1:64 (Normal Soil), 1:32 (Heavy Soil) Autoscrubber: 1:128 (Daily Use), 1:32 (Heavy Soil) Spray & Wipe: 1:64	903904*	
Stride® Citrus	1 x 5 gallon / 18.9 L Envirobox™/MC - Concentrate	1:32 (Heavy Soil), 1:64 (Normal Soil), 1:128 (Floors)	903906* (GGC)	
Stride® Citrus	6 x 32 oz. / 946 mL AccuMix® Containers -SC	Mop Bucket: 1:256 (Light Soil), 1:128 (Medium Soil) Autoscrubber: 1:768 (Light Soil), 1:384 (Medium Soil)	903909*	
Stride® Citrus	1 x 5 L / 1.32 gallon RTD® Unit (Fill) - SC	1:256 (Normal Soil)	93063390* (GGC)	
Stride® Citrus	2 x 2.5 L / 84.5 oz. J-Fill® Bottles - HC	1:375 (Normal Soil), 1:750 (Light Soil)	904716* (GGC)	
Stride® Citrus	2 x 1.4 L / 1.48 Qt. SmartDose™/MC Bottles - HC	1:375 (Mop Bucket), 1:750 (Autoscrubber)	95122613 (GGC)	

*Meets Green Seal's GS-37 standard.

*(GGC) Greenguard Certified

*Stride® Citrus Neutral Cleaner and Stride® Citrus SC Neutral Cleaner meet Green Seal® Standard GS-37 based on effective performance, concentrated volume, minimized/recycled packaging and protective limits on VOCs and human & environmental toxicity. GreenSeal.org.

*Stride® Citrus HC Neutral Cleaner meets Green Seal® Standard GS-37 based on effective performance, concentrated volume, minimized/recycled packaging and protective limits on VOCs and human & environmental toxicity. Acute toxicity damage met requirements at the as-used dilution, as specified for closed dilution systems. GreenSeal.org.

Safe handling

Please make sure your employees read and understand the product label and Safety Data Sheet before using this product. The label contains directions for use; and both the label and SDS contain hazard warnings, precautionary statements and first aid procedures. SDS are available online at www.diversey.com or by calling 888.352.2249. Improper use or dilution may result in damage to surfaces and may result in health and physical hazards that match those of the concentrate.

www.diversey.com

© 2019 Diversey, Inc. All Rights Reserved. PSS023 (19/199)