

Ready-to-Use



**Deodorizer • Disinfectant
Mildewstat • Virucide* • Sanitizer**



LAVENDER

- Multi-Purpose Cleaner
- Air Freshener
- Fabric Refresher
- Kills 99.99% of Germs[†] in 60 Seconds

ACTIVE INGREDIENTS:
Alkyl (C14 50%, C12 40%, C16 10%)
dimethyl benzyl ammonium chloride . . . 0.30%
OTHER INGREDIENTS: 99.70%
TOTAL: 100.00%

Item#	Packaging	Shipping Wt. (lbs.)	Cube Size (ft. ³)
910162-Q12	12x1 Quart	28	0.93



EPA Reg. No. 66243-1, EPA Est. No. 66243-GA-1 ESL03112021



Deodorizer • Disinfectant^s Mildewstat • Virucide* • Sanitizer

DIRECTIONS FOR USE

It is a violation of Federal law to use this product in a manner inconsistent with its labeling. This product is not for use on medical device surfaces.

WHERE TO USE

OdoBan® Ready-to-Use (RTU) is non-corrosive and non-staining to plastic, vinyl, synthetics, enamel, glazed tile and most common metals.

Can be used on nonporous surfaces such as walls, tables, floors, chairs, countertops, bathroom fixtures, sinks, shelves, racks, carts and other similar surfaces.

May be used in hospitals, medical and dental offices, nursing homes, day care centers, nurseries, restaurants and bars, cafeterias, institutional facilities, public restrooms, institutions, schools, athletic facilities, camp grounds, play grounds, public facilities, transportation terminals, hotels and motels, factories, business and office buildings, buses, ambulances, trains and taxis.

HOW TO APPLY

Spray 6-8 inches from surface, thoroughly wetting surfaces as recommended and required. For disinfecting or sanitizing, preclean with a cloth, sponge or brush. Do not breathe spray. Follow application directions.

DEODORIZER DIRECTIONS

AIR FRESHENER & FABRIC REFRESHER: Apply a light spray into the air, or onto surfaces such as upholstery, drapes, bedding, carpet, A/C filters, etc.

HARD SURFACES: Apply directly to odor source such as garbage pails, bedpans, hampers, toilets, shower curtains, fireplaces, athletic and work shoes, etc. Use in sick rooms, closets, basements or anywhere there are odors.

SOFT SURFACES: To control odor-causing bacteria on soft nonfood contact surfaces: Spray a light even coating on fabric until wet. DO NOT SATURATE. Let air dry. For difficult odors or heavy fabrics, repeat application. Reapply as necessary.

DISINFECTION DIRECTIONS

OdoBan® RTU is a Hospital Disinfectant for precleaned surfaces, Bactericidal according to the AOAC Use Dilution Test Method and a Mildewstat according to the EPA Mildew-Fungistatic guidelines in 10 minutes and Virucidal* according to the virucidal qualification in 60 seconds, against the following germs[†]:

Bacteria: *Pseudomonas aeruginosa*, *Staphylococcus aureus* (Staph), *Streptococcus pyogenes* (Strep), Methicillin Resistant *Staphylococcus aureus* (MRSA), Vancomycin Resistant *Enterococcus faecalis* (VREF), *Escherichia coli* (E.

coli) 0157:H7, *Listeria monocytogenes*, *Salmonella enterica*, *Serratia marcescens*, *Legionella pneumophila*

Fungi: *Aspergillus niger*, *Trichophyton interdigitale* (Athlete's foot fungus)

Viruses: *Herpes Simplex Type 2, **Human Coronavirus**, Influenza A H3N2.

DISINFECTION/VIRUCIDAL*: Apply solution after precleaning, thoroughly wetting hard nonporous surfaces as recommended and required, with a sprayer. Let stand 10 minutes for disinfection against bacteria and fungi or 60 seconds for disinfection against viruses*.

MOLD AND MILDEW CONTROL: To control mold and mildew on hard, nonporous, nonfood contact surfaces, wash visible soil from the surface. Then apply with trigger spray wetting all surfaces thoroughly. Let air dry. Repeat application every 7 days to control reoccurrence of growth.

SANITIZER DIRECTIONS

OdoBan® RTU is a sanitizer for precleaned, hard, nonporous, nonfood contact surfaces according to the method for Inanimate Non-Food Contact Surface Sanitizer in 60 seconds against the following germs[†]: *Streptococcus pyogenes* (Strep), *Escherichia coli* 0157:H7 (E. coli) (pathogenic strain), *Listeria monocytogenes*, *Staphylococcus aureus* (Staph), *Klebsiella pneumoniae*.

SANITIZING: Remove visible soil, then thoroughly preclean surfaces. To sanitize, apply to hard, nonporous, nonfood contact surfaces as required. Let stand 60 seconds then wipe.

STORAGE AND DISPOSAL

Store in areas inaccessible to small children. Do not reuse or refill this container. Offer for recycling, if available.

PRECAUTIONARY STATEMENTS

Hazards to Humans and Domestic Animals.

CAUTION—Causes moderate eye irritation. Avoid contact with eyes or clothing. Wash thoroughly with soap and water after handling.

FIRST AID

IF IN EYES: Hold eye open and rinse slowly and gently with water for 15-20 minutes. Remove contact lenses, if present, after the first 5 minutes, then continue rinsing eye. **IF ON SKIN OR CLOTHING:** Take off contaminated clothing. Rinse skin immediately with plenty of water for 15-20 minutes. Call a poison control center or doctor immediately for treatment advice. Have the product container or label with you when calling a poison control center or doctor, or going for treatment.

[†]When used according to disinfection/sanitization directions on hard, nonporous surfaces.