Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Portrait/Landscape Rotatable Fixed Flat-Screen Wall Mount for 37" to 70" TVs and Monitors

MODEL NUMBER: **DWM3770PLX**







Description

The VESA-compliant DWM3770PLX Portrait/Landscape Rotatable Fixed Flat-Screen Wall Mount allows you to mount your flat-panel television, monitor or other display on the wall. Recommended for home theaters, classrooms, boardrooms, hotels, bars and restaurants, it fits most flat-panel displays from 37 to 70 inches.

The DWM3770PLX effortlessly rotates 90 degrees to position your display in either portrait or landscape mode to fit your environment and comfort level. The durable all-metal frame with scratch-resistant powder-coated finish supports up to 110 pounds.

To ease wall installation, the VESA plate attached to the display slides down into the wall-mounted plate. Mounting hardware is included. A built-in bubble level allows accurate wall plate leveling. The DWM3770PLX conforms to VESA-compliant displays with any of the following mounting hole patterns: 200 x 200 mm, 300 x 300 mm, 400 x 200 mm, 400 x 400 mm and 600 x 400 mm.

Features

Mounts Your TV or Monitor to the Wall

- Fits most flat-panel televisions, monitors and other displays from 37 to 70 in.
- Recommended for home theaters, classrooms, boardrooms, hotels, bars and restaurants
- Mounting hardware included
- Display plate slides down into wall plate for easy wall-mounting

Allows 90° Rotation

- Spins effortlessly for portrait or landscape viewing

Durable Metal Construction

- Supports up to 110 lb.

Highlights

- Fits most flat-panel displays from 37 to 70 in.
- Rotates smoothly 90° from portrait to landscape and vice versa
- Slide-in VESA plate for easy mounting
- Durable metal construction
- Supports up to 110 lb.

Package Includes

- Wall plate
- Universal plate
- (2) Adapter brackets
- (4) M5 x 14 screws
- (4) M6 x 14 screws
- (4) M6 x 10 screws
- (4) M6 x 30 screws
- (4) M8 x 20 screws
- (4) M8 x 30 screws
- (4) Washers
- (4) D6 washers
- (8) Small spacers
- (4) Big spacers
- (4) Anchor bolts
- (4) Concrete anchors
- Hex key, 4 mm
- Owner’s manual

- Scratch-resistant powder-coated finish blends with any décor
- Built-in bubble level allows accurate display leveling

VESA Compliance

- Supports the following VESA mounting hole patterns: 200 x 200 mm, 300 x 300 mm, 400 x 200 mm, 400 x 400 mm and 600 x 400 mm

Specifications

PHYSICAL	
Mounting Location	Wall
Unit Dimensions (hwd / in.)	15.9 x 23.9 x 1.8
Unit Weight (lbs.)	9.75
Unit Weight (kg)	4.42
Material of Construction	Steel
Color	Black
Screen Size Compatibility (in.)	37 - 70
Screen Size Compatibility (cm)	94.1 - 178.0
VESA Pattern (mm)	200x200; 300x300; 400x200; 400x400; 600x400
Motion	Full
Distance from Wall (in.)	1.81
Distance from Wall (cm)	5
Maximum Weight Capacity (lbs.)	110
Maximum Weight Capacity (kg)	50
Distance from Wall (mm)	46
FEATURES & SPECIFICATIONS	
Tools Necessary	Yes
Cord Management	No
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: https://www.tripplite.com/products/product-certification-agencies