



021-4045

5K Swivel Stainless Steel Anchor

FEATURES :

- 180° / 360° rotating connection point
- Built with 316 stainless steel
- Measures 4-1/2" H x 3-1/2" W
- Minimum breaking strength 5,000 lbs.
- Fastener not included

FALL ARREST POINT(S) :

- 1 D-ring

ITEM WEIGHT :

- 1.8lbs (.82kg)



USER WEIGHT CAPACITY	
ANSI	130-310lbs (140.6kg)
OSHA	420lbs (190.5kg)

STANDARD COMPLIANT WITH	
ANSI	A10.32, Z359.18-2017 Type A
OSHA	1926.502, 1910.66

Replacement Part # (s)	
N/A	

COMPONENT	MATERIAL SPECIFICATION
Anchor	Stainless Steel