



## 021-4047

### 5K Swivel Steel Anchor & Bolt

**FEATURES :**

- 180° / 360° rotating connection point
- 1/2" x 4" steel bolt, washer and nut
- Installs quickly for temporary or permanent anchor point
- Used vertically or horizontally
- Minimum breaking strength 5,000 lbs.

**FALL ARREST POINT(S) :**

- 1 D-ring

**ITEM WEIGHT :**

- 1.2lbs (.5kg)



USER WEIGHT CAPACITY	
ANSI	130-310lbs (140.6kg)
OSHA	420lbs (190.5kg)

STANDARD COMPLIANT WITH	
ANSI	A10.32, Z359.18-2017 Type A
OSHA	1926.502, 1910.66

Replacement Part # (s)	
021-4062	5K Swivel Steel Anchor
021-4070	5K Swivel Anchor Bolt

COMPONENT	MATERIAL SPECIFICATION
Anchor	Zinc Plated Steel
Bolt	Zinc Plated Steel
Nut	Zinc Plated Steel
Washer	Zinc Plated Steel