

# HARSH DUTY 2-in-1 Utility Pump

UTM02505K

Submersible Utility Pump	1/4 нр	27 дрм		
Non-submersible Transfer Pump	1/4 нр	16 дрм		

## Features

- Designed to handle harsh liquids: Hot water up to 130°, Saltwater, Brine, Seawater, Soapy Water, Polypropylene Glycol Antifreeze\* and Soluble Oil Machine Tool Coolants\*
- Easily converts from a Submersible to Transfer pump with the suction strainer and suction hose, included
- Abrasion-resistant Nitrile rubber lip seal and gasket
- PPS thermoplastic impeller provides high temperature performance and mechanical strength
- 3/4" Garden hose threaded connection

## **Typical Applications**

- **Submersible:** Dewatering in coastal areas or salt-water marine areas; descaling; drain utility sinks, flooded basements, window wells, flat roofs, and pool covers.
- **Transfer:** Drain water heaters, boats, clogged sinks, water softeners, washing machines and utility sinks; fill radiant heating systems.



SUBMERSIBLE UTILITY Pumps down to 1/2"



NON-SUBMERSIBLE TRANSFER Pumps down to 1/16"



\*Transfer mode only

Dorformonoo

Performance									
			Discharge Flow (GPM)						
Model No. HP		HP	0'	5'	10'	15'	20'	25'	Max. lift
UTM02505K	Submersible	1/4	27	25	22	16	12	4	30'
	Transfer	1/4	16	14	12.2	10	6.7	2.8	30'

#### Information in this document is subject to change without notice.



### Application


Submersible utility pump	
Voltage	115
Hertz	60
Phase	Single
RPM	3450 RPM
Motor type	Permanent Split Capacitor (PSC)
Insulation	Class B
Circuit requirments	15 AMP
Duty rating	Continuous*
Shaft seal	Lip seal
Motor Shaft	Stainless steel
Upper motor bearing	Ball bearing
Lower motor bearing	Ball bearing
Cooling	Oil cooled
Motor protection	Auto reset thermal overload protector
*=	

\*For continuous,the water depth must be at least 6"to prevent the motor from overheating

#### **Pump Specifications**

3/4" garden hose			
10'			
SJTW 18AWG/3C ,UL list			
Reinforced thermoplastic			
Reinforced thermoplastic			
PPS Thermoplastic			
Nitrile rubber			
1/8" spherical			
32°-130°F			
Non-automatic			
Stainless steel			
27/16 GPM			
30 ft			
13.2 psi			

#### Performance



Model	HP	Amps	Discharge Height(ft)	0	5	10	15	20	25
Submersible	1/4	2.8	GPM	27	25	22	16	12	4
			GPH	1600	1500	1300	950	700	210
Transfer	1/4 2.8		GPM	16	14.0	12.2	10.0	6.7	2.8
		2.8	GPH	950	840	730	600	400	170

## Dimensions

