

Cast Iron

Sump and Effluent Pump

3 YEAR WARRANTY

SPI07508TPK

3/4 нр

Max. **76** FT

65 GPM

Features:

- Rugged cast iron pump housing, pump base and motor housing.
- Energy-efficient, PSC motor with thermal overload protection.
- Oil-filled motor for maximum heat dissipation and permanent lubrication.
- Ball bearings for quiet operation.
- Non clog vortex impeller handles up to 3/4" spherical solids
- Piggyback Tethered Float Switch for automatic or manual operation.
- Operates up to 130°F in water transfer or dewatering applications.
- 1-1/2" NPT Discharge with 20' power cord.

Typical Applications

- Light Commercial dewatering
- Water transfer
- STEP or onsite applications
- Low pressure pipe (LPP)








Performance

	Discharge Flow(GPM)											
Model No.	HP	0'	5'	10'	20'	30'	40'	50'	60'	70'	Max. lift	
SPI07508TPK	3/4	65	62	59	52	45	37	28	19	7	76'	




Application	
STEP or onsite applicationsWater transferLight commercial dewatering	
Voltage	115
Hertz	60
Phase	Single
RPM	3450 RPM
Motor type	Permanent Split Capacitor(PSC
Insulation	Class B
Circuit requirments	20 AMP
Duty rating	Continuous*
Shaft seal	Mechanical seal Carbon/Sic,NBR
Motor Shaft	Stainless steel
Upper motor bearing	Ball bearing
Lower motor bearing	Ball bearing
Cooling	oil cooled
Motor protection	Auto reset thermal overload protector
Pump Specifications	
Discharge size	1-1/2" NPT
Pump Housing	Cast iron
Pump Base	Cast iron
Motor Housing	Cast iron
Impeller material	Thermoplastic, single vane
Liquid temp.range	32°-130°F
Fasteners	Steel
Solids handling	3/4" spherical solids
Max Head	76'
Cord Length	20 FT cord
Cord type	SJOW 16AWG/3C, UL list

Performance



	Model	HP	Amps	Discharge Height(ft)	0	5	10	20	30	40	50	60	70
[SPI07508TPK	3/4	12	GPM	65	62	59	52	45	37	28	19	7

Dimensions



Automatic Switch Specifications

Wide Angle Tethered

20 FT cord

Reinforced thermoplastic

SJOW 16AWG/3C, UL list

Туре

Material

Cord Length

Cord type