



Main

Product	Double Throw Safety Switch
Duty Rating	General duty
Disconnect Type	Non-fusible disconnect
Factory Installed Neutral	None
Number of Poles	4
Current Rating	200 A
Voltage Rating	600 V AC 600 V DC
Enclosure Rating	NEMA 3R

Complementary

Short-circuit current	10 kA H or J
Fuse type	H or J
Mounting Type	Surface
Wire Size	AWG 6...300 kcmil copper or aluminium
Tightening torque	340 lbf.in (38.41 N.m) (AWG 6...300 kcmil)
Depth	10.63 in (270.00 mm)
Width	33.02 in (838.71 mm)
Height	38 in (965.20 mm)
Net Weight	104.94 lb(US) (47.6 kg)

Environment

Certifications	UL Listed
----------------	-----------

Ordering and shipping details

Category	00133 - DT SWITCH,NEMA3R
Discount Schedule	DE1
GTIN	00785901501701
Nbr. of units in pkg.	1
Package weight(Lbs)	105 lb(US) (47.63 kg)
Returnability	No
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	14.96 in (38.001 cm)
Package 1 width	13.00 in (33.02 cm)
Package 1 Length	4.19 in (10.63 cm)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------