

Product data sheet

Characteristics

UTRS213AFL

Individual meter socket, ringless socket, no bypass, 4 jaws no release, UG, 200 A, up to 600 VAC single phase 3W



Main

Product or component type	Meter Socket
Meter socket type	Ringless

Complementary

Meter socket rated current	200 A
Number of jaws	4
Bypass type	No bypass
Phase	1 phase
[Ue] rated operational voltage	600 V AC
Enclosure material	Steel
Service feed location	UG
Wiring configuration	3-wire

Environment

Product certifications	UL Listed
Enclosure Rating	NEMA 3R

Ordering and shipping details

Category	00039 - METER SOCKETS & HUBS
Discount Schedule	DE4
GTIN	00785901559061
Nbr. of units in pkg.	1
Package weight(Lbs)	24 lb(US) (10.89 kg)
Returnability	Yes
Country of origin	US

Packing Units

Package 1 Height	15.00 in (38.100 cm)
Package 1 width	11.00 in (27.940 cm)
Package 1 Length	4.40 in (11.176 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Nickel (Metallic), which is known to the State of California to cause cancer, and Toluene, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Under investigation