



Main

Range of product	Altivar
Product or component type	Encoder interface module
Range compatibility	Altivar Process ATV900 Altivar Process Modular Altivar Machine ATV340
Encoder type	Resolver

Complementary

Maximum supply current	0.05 A
Protection type	Overload protection Short-circuit protection
Maximum cable distance between devices	328.08 ft (100 m)
Maximum operating frequency	12 kHz
Input signal	Sin+, Sin-, Cos+, Cos-, Temp+, Temp-
Output signal	Ref+, Ref-
Ratio	3/10, 1/2, 3/4, 1
Connector type	1 female SUB-D 9
Net Weight	0.33 lb(US) (0.15 kg)

Ordering and shipping details

Category	22209 - ATV650
Discount Schedule	CP4E
GTIN	00785901676720
Nbr. of units in pkg.	1
Package weight(Lbs)	0.34 lb(US) (0.15 kg)
Returnability	Yes
Country of origin	ID

Packing Units

Package 1 Height	0.660 dm
Package 1 width	1.300 dm
Package 1 Length	1.900 dm

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
RECh Regulation	RECh Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes

RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
PVC free	Yes