



Main

Range	I-Line
Product or Component Type	Drip hood

Complementary

Width	12.016 in (305.21 mm)
Height	44.2 in (1122.68 mm)
Depth	2.52 in (64.01 mm)
Product Destination	Panelboard HCR-U 44 in (1117.60 mm) 86 in (2184.40 mm) 9.5 in (241.30 mm)
Device Mounting	Surface

Environment

Standards	CE CULus
-----------	-------------

Ordering and shipping details

Category	00016-I-LINE PB RTA
Discount Schedule	PE1A
GTIN	00785901706090
Package weight(Lbs)	14.39 lb(US) (6.527 kg)
Returnability	Yes
Country of origin	US

Packing Units

Package 1 Height	0.52 ft (0.160 m)
Package 1 width	1.17 ft (0.356 m)
Package 1 Length	3.92 ft (1.196 m)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Environmental Disclosure	Product Environmental Profile
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------
