



## Main

|                           |                          |
|---------------------------|--------------------------|
| Range of product          | Harmony 9001B            |
| Product or component type | Complete control station |
| Device short name         | 9001BR                   |

## Complementary

|                                |                           |
|--------------------------------|---------------------------|
| Control station composition    | 2 push-buttons START-STOP |
| Contacts type and composition  | 1 NO + 1 NC               |
| Connections - terminals        | Screw clamp terminal      |
| [Ie] rated operational current | 5 A 600 V                 |
| Device mounting                | Surface                   |
| Type of installation           | Indoor                    |

## Environment

|                              |   |
|------------------------------|---|
| NEMA degree of protection    | NEMA 7/9  |
| Product certifications       | CE<br>CSA LR25490 class 3211 03<br>UL listed file E42259 CCN NKCR |
| Environmental characteristic | Hazardous location  |

## Ordering and shipping details

|                       |                                  |
|-----------------------|----------------------------------|
| Category              | 21421 - 9001 B (NOT BW70 - BW80) |
| Discount Schedule     | CS1                              |
| GTIN                  | 00785901600886                   |
| Nbr. of units in pkg. | 1                                |
| Package weight(Lbs)   | 3.57 lb(US) (1.62 kg)            |
| Returnability         | Yes                              |
| Country of origin     | MX                               |

## Packing Units

|                  |                      |
|------------------|----------------------|
| Package 1 Height | 13.97 in (35.484 cm) |
| Package 1 width  | 5.50 in (13.970 cm)  |
| Package 1 Length | 35.48 in (90.129 cm) |

## Offer Sustainability

|                            |  |
|----------------------------|--|
| Sustainable offer status   | Green Premium product  |
| California proposition 65  | WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| REACH free of SVHC         | Yes  |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>   |
| Toxic heavy metal free     | Yes  |
| Mercury free               | Yes  |
| RoHS exemption information | <a href="#">Yes</a>  |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>   |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>  |
| Circularity Profile        | <a href="#">End Of Life Information</a>  |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|