



Main

| | |
|------------------|----------|
| Range | 9080LB |
| Product | Cover |
| Fixing Mode | Screwed |
| Quantity per set | Set of 5 |

Complementary

| | |
|--------|--------------------|
| Height | 3.38 in (85.85 mm) |
| Width | 1.78 in (45.21 mm) |
| Depth | 0.06 in (1.52 mm) |

Ordering and shipping details

| | |
|-----------------------|-----------------------|
| Category | 21711 - 9080 LB |
| Discount Schedule | CP1 |
| GTIN | 00785901180999 |
| Nbr. of units in pkg. | 5 |
| Package weight(Lbs) | 0.02 lb(US) (0.01 kg) |
| Returnability | Yes |
| Country of origin | US |

Packing Units

| | |
|------------------|--------------------|
| Package 1 Height | 1.80 in (4.572 cm) |
| Package 1 width | 3.40 in (8.636 cm) |
| Package 1 Length | 0.10 in (0.254 cm) |

Offer Sustainability

| | |
|----------------------------|---|
| California proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|