



## Main

Product or component type	Circuit breaker
Trip Unit Technology	Thermal-magnetic

## Complementary

Line Rated Current	400 A
Number of Poles	2P
Breaking capacity code	H
Mounting Mode	I-Line
Wiring Configuration	2-wire
Magnetic Hold Current	2000 A
Magnetic Tripping Current	4000 A
Electrical connection	Lugs load I-Line connection line
Terminal identifier	AL400LA
Tightening torque	115.06 Lbf.in (13 N.m) 0.07...0.47 in <sup>2</sup> (42...304 mm <sup>2</sup> ) (AWG 1...600 kcmil) 115.06 lbf.in (13 N.m) 0.07...0.20 in <sup>2</sup> (42...127 mm <sup>2</sup> ) (AWG 1...250 kcmil)
Phase connection	AC
Height	11 in (279.40 mm)
Width	6 in (152.40 mm)
Depth	5.84 in (148.34 mm)

## Environment

Certifications	UL Listed CSA
----------------	------------------

## Ordering and shipping details

Category	01040 - LA/LH BRKR, SW, MAG-GARD
Discount Schedule	DE2
GTIN	00785901358725
Nbr. of units in pkg.	1
Package weight(Lbs)	16.23 lb(US) (7.36 kg)
Returnability	Yes
Country of origin	MX

## Packing Units

Package 1 Height	9.00 in (22.860 cm)
Package 1 width	11.70 in (29.718 cm)
Package 1 Length	17.80 in (45.212 cm)

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
PVC free	Yes
Halogen content performance	Halogen free plastic parts product

## Contractual warranty

Warranty	18 months
----------	-----------