



### Main

Product or component type	Additional output module
Range compatibility	Altivar Machine ATV340 Easy Altivar 610 Altivar Process ATV900 Altivar Process ATV600
Input/output type	3 relay output
Discrete output number	3
Discrete output type	R4, R5, R6) relay normally open 1 ms

### Complementary

Electrical durability	100000 cycles
Minimum switching current	5 mA 24 V DC
Maximum switching current	2 A 250 V AC inductive, cos phi = 0.4 5 ms 2 A 30 V DC inductive, cos phi = 0.4 5 ms 5 A 250 V AC resistive, cos phi = 1 5 ms 5 A 30 V DC resistive, cos phi = 1 5 ms
Electrical connection	Screw terminal block, 1.5 mm <sup>2</sup> / AWG 16, 4.43 lbf.in (0.5 N.m)
Net Weight	0.88 lb(US) (0.4 kg)

### Ordering and shipping details

Category	22207 - ATV630 FRAMES 5 & 6
Discount Schedule	CP4E
GTIN	00785901969211
Nbr. of units in pkg.	1
Package weight(Lbs)	0.31 lb(US) (0.14 kg)
Returnability	Yes
Country of origin	ID

### Packing Units

Package 1 Height	0.650 dm
Package 1 width	1.300 dm
Package 1 Length	1.900 dm

### Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>