

Product Datasheet

Self-contained pressurized eye wash - 15 US gal 15GEW

15 US gallon (56.8 liter) portable eye/face wash unit incorporating a stainless steel cylinder is capable of washing eyes and face simultaneously for up to 15 minutes. Featuring dust covers and push lever operation for ease of use.

For decontamination of body parts subjected to minor contamination, an optional drench hose for eye, face and body washing can be fitted. Includes inspection tag for recording test and service history, ANSI compliant.



Specifications

BODY	
MATERIAL	Stainless steel cylinder
CAPACITY	15 US gal (56.8 L)
SERVICES	
OPERATING PRESSURE	2.1 to 5.5 BAR G (30-80 PSI)
TEST PRESSURE	6.2 BAR G (90 PSI)
FLOW RATE	1.5 liters per minute (0.4 gpm)
OPERATION DURATION	15 minutes
HOSE CONNECTION	½ in female NPT
AMBIENT OPERATING TEMPERATURE	
MINIMUM	5C (41F)
MAXIMUM	35C (95F)
OPERATION	
EYE WASH	Push plate
COLOR	Green
SHAPE	Circular
DIMENSIONS & WEIGHT	
DIMENSIONS (HxWxD)	1047mm (41.2in) x 404mm (15.9) x 404mm (15.9)
WEIGHT	Empty: 20kg / 44lb empty, Full: 58kg / 127lb

General Arrangement Drawing

Self-contained pressurized eye wash - 15 US gal

15GEW

