

Product Datasheet

Removable insulated (15GEW-BLKT) or heated and insulated (15GEW-BLKT-HT) cover

for the 15GEW self-contained eye/face wash

Insulated or heated and insulated covers for use with the 15GEW self-contained eye wash when located outdoors during the colder seasons to offer frost protection.

The 15 US gallon (56.8 liter) portable eye/face wash unit incorporating a stainless steel cylinder is capable of washing eyes and face simultaneously for up to 15 minutes. Featuring dust covers and push lever operation for ease of use. For decontamination of body parts subjected to minor contamination, an optional drench hose for eye, face and body washing can be fitted. Includes inspection tag for recording test and service history, ANSI compliant.

- Constructed from heavyweight PVC cloth
- Double stitched to provide extended durability
- Simple to fit via the velcro fastenings
- Choice of insulated cover or heated and insulated cover



Specifications

INSULATED COVER	
OUTER FABRIC	PE560, grey PVC coated Polyester with A4 data pouch
INSULATION	50mm mineral wool
INNER FABRIC	Silicone coated glass cloth
FASTENINGS	FR hook and loop
DOCUMENT POUCH	Zipped A4
DIMENSIONS (packaged)	21in x 26in x 10in

INSULATED AND HEATED COVER	
OUTER FABRIC	PE560, grey PVC coated Polyester with A4 data pouch
INSULATION	50mm mineral wool
INNER FABRIC	Silicone coated glass cloth
FASTENINGS	FR hook and loop
VOLTAGE	110V
POWER RATING	75W
HEAT SOURCE	PSB 15 UL approved self-regulating cable
OVERHEAT PROTECTION	UL approved 89.6F (32C) PEPI thermostat
AMBIENT TEMPERATURE RATINGS	Keeps water tepid at 68F (20C) - operates in temperatures as low as -4F (-20C)
CONNECTING CABLE	2m x 3 core cable
DIMENSIONS (packaged)	21in x 26in x 10in