

Product data sheet

Characteristics

RDB62

Wireway, Square-Duct, raintight trough, 6 inch by 6 inch, 2 feet long, NEMA 3R



Main

Busbar description	Straight length
Device short name	RDB
Enclosure type	Rainproof enclosure indoor/outdoor Ice/sleet proof enclosure indoor/outdoor
Provided equipment	Removable cover sealable
Range of product	SQUARE-Duct

Complementary

Enclosure material	16 gauge steel
Length	2 ft (0.61 m)
Surface finish	Gray polyester powder ANSI 49
Trunking dimension	6 x 6 in

Environment

NEMA degree of protection	NEMA 3R
Product certifications	UL Listed

Ordering and shipping details

Category	01422 - RDB WIREWAY, NEMA 3R
Discount Schedule	PE9
GTIN	00785901046844
Nbr. of units in pkg.	1
Package weight(Lbs)	14 lb(US) (6.35 kg)
Returnability	Yes
Country of origin	MX

Packing Units

Package 1 Height	6.60 in (16.764 cm)
Package 1 width	7.00 in (17.780 cm)
Package 1 Length	26.50 in (67.310 cm)

Offer Sustainability

EU RoHS Directive	Not applicable, out of EU RoHS legal scope
China RoHS Regulation	China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------