



## Main

Range	I-Line
Product or Component Type	Drip hood

## Complementary

Rated Operational Voltage	600 V AC/DC 50/60 Hz
Height	26 in (660.40 mm)
Width	8.943 in (227.15 mm)
Depth	2.52 in (64.01 mm)

## Environment

NEMA Rating	NEMA 2
-------------	--------




## Ordering and shipping details

Category	00016 - I-LINE PB RTA
Discount Schedule	PE1A
GTIN	00785901501442
Nbr. of units in pkg.	1
Package weight(Lbs)	7.41 lb(US) (3.36 kg)
Returnability	No
Country of origin	US

## Packing Units

Package 1 Height	6.40 in (16.256 cm)
Package 1 width	14.00 in (35.560 cm)
Package 1 Length	32.20 in (81.788 cm)

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>

Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
PVC free	Yes
<b>Contractual warranty</b>	
Warranty	18 months