


8736SCO7V02S

NEMA Starter, Type S, reversing, vertical,
Size 1, 27A, 10 HP at 575 VAC, 5 kA SSCR, 3
phase, 3 pole, melting alloy overload, 120 VAC
coil, open



Main

Product Type	Starter
Product Range	S
Starter Type	Reversing

Complementary

NEMA Size	1
Rated Current	27 A
Number of Poles	3P
Mounting Orientation	Vertical
Wiring Mode	3 wires
Maximum Voltage Rating	600 V AC
Phase	3 phase
Type of Overload	Melting alloy 3
Horsepower Rating	7.5 HP 200 V AC 7.5 HP 230 V AC 10 HP 460 V AC 10 HP 575 V AC
SCCR	Circuit-breaker: 5 kA at 600 V AC Fuse: 5 kA at 600 V AC
Coil Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Control Circuit Type	Separate control circuit
Control Units	No control units
Pilot Light	Without pilot light
Auxiliary Contacts	Without
Terminal Type	Screw clamp terminals
Height	11.52 in (292.61 mm)
Width	5.47 in (138.94 mm)
Depth	5.31 in (134.87 mm)

Environment

Enclosure Type	Not rated (open device)
Certifications	UL Listed CSA

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Ordering and shipping details

Category	21272 - 8702,36 SC,SD(NOT S*R,T,W)
Discount Schedule	CP1
GTIN	00785901874409
Nbr. of units in pkg.	1
Package weight(Lbs)	10.48 lb(US) (4.754 kg)
Returnability	Yes
Country of origin	MX

Packing Units

Package 1 Height	8.60 in (21.844 cm)
Package 1 width	11.30 in (28.702 cm)
Package 1 Length	13.80 in (35.052 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Not compliant
China RoHS Regulation	 China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------