



Main

Product Type	Load Center Cover
Marketing Trade Name	Homeline
Cover Type	Combination flush/surface cover

Complementary

Number of Spaces	20
Surface Finish	Baked enamel grey
Height	31.06 in (788.92 mm)
Width	15.44 in (392.18 mm)
Tightening Torque	Screw 2.3 N.m

Ordering and shipping details

Category	00183 - HOM LC REPLACEMENT COVERS
Discount Schedule	DE5
GTIN	00785901077527
Nbr. of units in pkg.	1
Package weight(Lbs)	10.7 lb(US) (4.85 kg)
Returnability	Yes
Country of origin	US

Packing Units

Package 1 Height	1.30 in (3.302 cm)
Package 1 width	15.80 in (40.132 cm)
Package 1 Length	31.20 in (79.248 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty

Lifetime
