



Main

| | |
|---------------------------|------------------|
| Range | PowerPact |
| Product or component type | Circuit breaker |
| Trip Unit Technology | Thermal-magnetic |

Complementary

| | |
|---------------------------|--|
| Line Rated Current | 200 A |
| Number of Poles | 2P |
| Mounting Mode | Unit mount |
| Magnetic Hold Current | 1000 A |
| Magnetic Tripping Current | 2000 A |
| Operator | Short lever |
| Electrical connection | Lugs load Lugs line |
| Terminal identifier | AL400LA |
| Tightening torque | 115.06 Lbf.in (13 N.m) 0.07...0.47 in ² (42...304 mm ²) (AWG 1...600 kcmil) 115.06 lbf.in (13 N.m) 0.07...0.20 in ² (42...127 mm ²) (AWG 1...250 kcmil) |
| Height | 11 in (279.40 mm) |
| Width | 6 in (152.40 mm) |
| Depth | 5.84 in (148.34 mm) |

Environment

| | |
|----------------|-------------------------|
| Certifications | IEC UL Listed CSA |
|----------------|-------------------------|

Ordering and shipping details

| | |
|-----------------------|------------------------------------|
| Category | 00935 - LAL/LHL BRKR, SW, MAG-GARD |
| Discount Schedule | DE2 |
| GTIN | 00785901402428 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 14.27 lb(US) (6.47 kg) |
| Returnability | No |
| Country of origin | MX |

Offer Sustainability

| | |
|-----------------------------|--|
| Sustainable offer status | Green Premium product |
| California proposition 65 | WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |
| PVC free | Yes |
| Halogen content performance | Halogen free plastic parts product |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|