






|                                                                                                                                                                                 |  |                                                                                                                                                                                                                                                                                                                                                                                                                                                |  |                                                                              |                                                  |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|------------------------------------------------------------------------------|--------------------------------------------------|
|  <p>Zoro Tools, Inc.<br/>500 W Madison St, Chicago, IL 60661, USA<br/>Ph: (855) 289-9676</p> |  | <p>This file and any associated information and specifications are provided for reference and evaluation purposes only, and is subject to change without notice. Zoro makes no representations, warranties or guarantees as to the appropriateness, accuracy, completeness, or suitability for any purpose, of the file, information or specifications. You are solely responsible for the use of the file, information or specifications.</p> |  | <p><b>COMPONENT</b> Socket Head Cap Screw</p>                                |                                                  |
|                                                                                                                                                                                 |  |                                                                                                                                                                                                                                                                                                                                                                                                                                                |  | <p><b>G6177281</b></p>                                                       |                                                  |
|                                                                                                                                                                                 |  |                                                                                                                                                                                                                                                                                                                                                                                                                                                |  | <p>M14-2.00 Socket Head Cap Screw,<br/>Black Oxide Steel, 50 mm L, 25 PK</p> |                                                  |
|                                                                                                                                                                                 |  |                                                                                                                                                                                                                                                                                                                                                                                                                                                |  | <p><b>SCALE</b> 1.64</p>                                                     | <p><b>UNIT</b> MM</p> <p><b>SHEET</b> 1 of 1</p> |