



### Main

Product or component type	Shunt trip
Circuit breaker type	H-frame J-frame L-Frame

### Complementary

Rated voltage	208...277 V AC
Tightening torque	12.39 lbf.in (1.4 N.m) 0.00...0.00 in <sup>2</sup> (0.82...2.5 mm <sup>2</sup> ) (AWG 18...AWG 14)

### Environment

Product certifications	CSA
------------------------	-----

### Ordering and shipping details

Category	01103 - H,J,COMPACT NS UL/IEC CIRCUIT BREAKER ACCESSORIES
Discount Schedule	DE2
GTIN	00785901545675
Nbr. of units in pkg.	1
Package weight(Lbs)	0.29 lb(US) (0.13 kg)
Returnability	Yes
Country of origin	US

### Packing Units

Package 1 Height	1.70 in (4.318 cm)
Package 1 width	2.90 in (7.366 cm)
Package 1 Length	4.40 in (11.176 cm)

### Offer Sustainability

EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

### Contractual warranty

Warranty	18 months
----------	-----------