

Product data sheet

Characteristics

8910DPAG63V02

Contacteur, Definite Purpose, 60A, 3 pole, 30 HP at 575 VAC, 3 phase, 110/120 VAC 50/60 Hz coil, NEMA 1



Main

Product or component type	Definite Purpose Contactor
Line Rated Current	60 A
Number of Poles	3P
Pole contact composition	3 NO
Range of product	DPA
Provided equipment	Enclosure
Enclosure type	NEMA type 1

Complementary

Maximum Horse Power Rating	5 Hp 115 V AC, 1 phase 10 Hp 230 V AC, 1 phase 30 Hp 460 V AC, 3 phase 30 Hp 575 V AC, 3 phase 25 hp 230 V AC, 3 phase
Locked rotor rated current	360 A 277 V AC 300 A 460 V AC 240 A 575 V AC
[Ue] rated operational voltage	600 V AC
[Uc] control circuit voltage	120 V AC 60 Hz 110 V AC 50 Hz
Phase	3 phase
Electrical connection	Box lugs Quick connect terminals
Height	12.69 in (322.33 mm)
Width	27.81 in (706.37 mm)
Depth	6.31 in (160.27 mm)

Environment

Product certifications	UL Recognized CSA
------------------------	----------------------

Ordering and shipping details

Category	21346 - 8910 DPA 6_(60 AMP)
Discount Schedule	CP1B
GTIN	00785901325277
Nbr. of units in pkg.	1
Package weight(Lbs)	8.4 lb(US) (3.81 kg)
Returnability	Yes
Country of origin	CN

Packing Units

Package 1 Height	7.20 in (18.288 cm)
Package 1 width	9.00 in (22.860 cm)
Package 1 Length	13.40 in (34.036 cm)

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------