



Main

Product	Circuit breaker
Range	QO
Current Rating	15 A
Voltage Rating	120/240 V AC
Mounting Type	Plug-in
Number of Poles	1P
Circuit Breaker Type	Standard
Ratings	HACR rated
Electrical Connection	Box lugs

Complementary

Interrupt Rating	10 kA 120/240 V AC 50/60 Hz
Number of Panel Spaces	1
Provided Equipment	18 in (457.20 mm) lead
Wire Size	AWG 12...AWG 2 aluminium AWG 14...AWG 2 copper
Tightening Torque	40.71 lbf.in (4.6 N.m)
Height	4.55 in (115.57 mm)
Width	0.75 in (19.05 mm)
Depth	2.91 in (73.91 mm)

Environment

Certifications	UL Listed CSA
Ambient Rating	104 °F (40 °C)

Ordering and shipping details

Category	09650 - POWERLINK QO(B)PL BREAKERS
Discount Schedule	DE8A
GTIN	00785901095699
Nbr. of units in pkg.	1
Package weight(Lbs)	0.5 lb(US) (0.23 kg)
Returnability	Yes
Country of origin	MX

Packing Units

Package 1 Height	1.30 in (3.302 cm)
Package 1 width	4.00 in (10.160 cm)
Package 1 Length	5.50 in (13.970 cm)

Offer Sustainability

California proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Halogen content performance	Halogen free product

Contractual warranty

Warranty	18 months
----------	-----------