

Product data sheet

Characteristics

UTRS213CFL

Individual meter socket, ringless socket, no bypass, 4 jaws no release, OH, UG, 200 A, up to 600 VAC single phase 3W



Main

Product or component type	Meter Socket
Meter socket type	Ringless

Complementary

Meter socket rated current	200 A
Number of jaws	4
Bypass type	No bypass
Phase	1 phase
[Ue] rated operational voltage	600 V AC
Enclosure material	Steel
Service feed location	UG OH
Wiring configuration	3-wire
Device mounting	Surface

Environment

Product certifications	UL Listed
Enclosure Rating	NEMA 3R

Ordering and shipping details

Category	00039 - METER SOCKETS & HUBS
Discount Schedule	DE4
GTIN	00785901577447
Nbr. of units in pkg.	1
Package weight(Lbs)	12.83 lb(US) (5.82 kg)
Returnability	Yes
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	5.50 in (13.97 cm)
Package 1 width	12.00 in (30.48 cm)
Package 1 Length	16.00 in (40.64 cm)
Unit Type of Package 2	PAL
Number of Units in Package 2	72
Package 2 Weight	948.00 lb(US) (430.005 kg)
Package 2 Height	39.50 in (100.33 cm)

Package 2 width	44.00 in (111.76 cm)
Package 2 Length	48.00 in (121.92 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Nickel (Metallic), which is known to the State of California to cause cancer, and Toluene, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Under investigation

Contractual warranty

Warranty	18 months
----------	-----------