



### Main

Product or component type	Industrial Control Transformer
Range of product	Instakits

### Complementary

Phase	1 phase 3 phase
Rated power in VA	50 VA
Primary voltage	600 V
Secondary voltage	120 V
Electrical connection	Connector

### Environment

Product certifications	UL CSA
------------------------	-----------

### Ordering and shipping details

Category	22341 - CONTACTOR,D,K,&F ACCESS
Discount Schedule	I12
GTIN	00785901875635
Nbr. of units in pkg.	1
Package weight(Lbs)	3.37 lb(US) (1.53 kg)
Returnability	Yes
Country of origin	MX

### Packing Units

Package 1 Height	6.40 in (16.256 cm)
Package 1 width	6.90 in (17.526 cm)
Package 1 Length	7.90 in (20.066 cm)

### Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
PVC free	Yes

## Contractual warranty

---

Warranty

18 months

---