



## Main

Product Type	Sub-feed lug
Marketing Trade Name	QO
Rated Current	125 A
Number of Spaces	3
Number of Phases	3 phase
Voltage Rating	240 V AC

## Complementary

Number of Poles	3
Wire Size	AWG 12...AWG 2/0 copper or aluminium
Product Certifications	CSA CURus
Mounting Mode	Bolt-on
Height	3.500 in (88.90 mm)
Width	2.241 in (56.92 mm)
Depth	2.310 in (58.67 mm)

## Environment

Ambient Air Temperature for Operation	23 °F (-5 °C) 104 °F (40 °C)
---------------------------------------	---------------------------------

## Ordering and shipping details

Category	00015 - QOB CIRCUIT BREAKERS
Discount Schedule	DE2
GTIN	00785901031345
Nbr. of units in pkg.	1
Package weight(Lbs)	0.88 lb(US) (0.40 kg)
Returnability	Yes
Country of origin	MX

## Packing Units

Package 1 Height	2.30 in (5.842 cm)
Package 1 width	4.00 in (10.160 cm)
Package 1 Length	3.40 in (8.636 cm)

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes

RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Halogen content performance	Halogen free product

### Contractual warranty

Warranty	18 months
----------	-----------