

9070TF300D2

Transformer, Type TF, industrial control, 300 VA, 240/480 VAC primary / 24 VDC secondary, 1 phase, 50/60 Hz, 80 °C rise



Main

Product or component type	Industrial Control Transformer
Power Rating	300 VA
Primary Voltage	240 x 480 V
Secondary Voltage	24 V
Type	TF

Complementary

Number of Phases	1 phase
Power Rating	300 VA UL 300 VA CSA 300 VA NOM 200 VA
Primary to Secondary Voltage	240 x 480 V 24 V
Fuse type	10.3 x 38 mm CC top
Temperature rise	80 °C
Electrical connection	Screw clamp terminals

Environment

Product certifications	UL Listed CSA
Enclosure Type	Not rated (open device)
Insulation temperature	266 °F (130 °C)

Ordering and shipping details

Category	16207 - 9070 TF (NOT T) MTO
Discount Schedule	CP8
GTIN	00785901322245
Nbr. of units in pkg.	1
Package weight(Lbs)	1 lb(US) (0.45 kg)
Returnability	No
Country of origin	US

Packing Units

Package 1 Height	6.50 in (16.510 cm)
Package 1 width	6.70 in (17.018 cm)
Package 1 Length	7.50 in (19.050 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------