

Product data sheet

Characteristics

EZM1600TB

EZ Meter Pak, center main unit, OH, UG, 600 A, 120/240 VAC single phase, 3W, main lugs, N3R, busbar, Al



Main

Range of product	EZ meter-pak
Product or component type	Meter center main unit
Main type	Main Lugs
Included Items	Box

Complementary

Main rated current	600 A
Bus rated current	800 A
Material	Aluminium busbar
Enclosure material	Steel
[Ue] rated operational voltage	120/240 V AC
Device mounting	Surface
Number of Phases	1 phase in 1 phase out
Service feed location	OH UG
Electrical connection	Lugs 1 AWG 6...300 kcmil aluminium/copper) ground Lugs 2 AWG 1/0...750 kcmil aluminium/copper) line Lugs 4 AWG 1/0...300 kcmil aluminium/copper) line Lugs 2 AWG 1/0...750 kcmil aluminium/copper) neutral Lugs 4 AWG 1/0...300 kcmil aluminium/copper) neutral
Wiring configuration	3-wire
Height	30.46 in (773.68 mm)
Width	17.15 in (435.61 mm)
Depth	7.09 in (180.09 mm)

Environment

Product certifications	UL Listed
Enclosure Rating	NEMA 3R

Ordering and shipping details

Category	00020 - EZ METER-PAK
Discount Schedule	DE4
GTIN	00785901295976
Nbr. of units in pkg.	1
Package weight(Lbs)	45.32 lb(US) (20.56 kg)
Returnability	Yes
Country of origin	MX

Packing Units

Package 1 Height	8.00 in (20.320 cm)
Package 1 width	21.00 in (53.340 cm)
Package 1 Length	31.30 in (79.502 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes

Contractual warranty

Warranty	18 months
----------	-----------