

Product data sheet

Characteristics

XACB911

boot with circlip XAC-B - for booted operator - polychloroprene - 4 mm



Main

Range of product	Harmony XAC
Accessory / separate part designation	Boot with circlip
Accessory / separate part type	Boot
Accessory / separate part category	Separate parts
Product compatibility	XACB91.
Accessory / separate part destination	Booted operator
Operating travel	0.16 in (4 mm)
Material	Polychloroprene
Sale per indivisible quantity	10

Complementary

Net Weight	0.00 lb(US) (0.002 kg)
------------	------------------------

Environment

Ambient air temperature for operation	-13...158 °F (-25...70 °C)
---------------------------------------	----------------------------

Ordering and shipping details

Category	22473 - PUSHBUTTON, PENDANTS
Discount Schedule	CS2
GTIN	00785901640776
Nbr. of units in pkg.	10
Package weight(Lbs)	0.01 lb(US) (0.00 kg)
Returnability	Yes
Country of origin	CZ

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	1.18 in (3 cm)
Package 1 width	1.97 in (5 cm)
Package 1 Length	3.15 in (8 cm)
Unit Type of Package 2	BAG
Number of Units in Package 2	10
Package 2 Weight	1.38 oz (39 g)
Package 2 Height	1.18 in (3 cm)
Package 2 width	1.97 in (5 cm)
Package 2 Length	3.15 in (8 cm)
Unit Type of Package 3	S01
Number of Units in Package 3	150
Package 3 Weight	28.01 oz (794 g)
Package 3 Height	5.91 in (15 cm)
Package 3 width	5.91 in (15 cm)
Package 3 Length	15.75 in (40 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------