



Main

Marketing Trade Name	QO
Product Type	Load Center Cover

Complementary

Cover Type	Surface cover
Product Compatibility	For indoor load center
Surface Finish	Baked enamel Gray
Number of Spaces	16
Height	17.92 in (455.17 mm)
Width	14.24 in (361.70 mm)
Depth	0.7 in (17.8 mm)
Tightening Torque	Cover 2.3 N.m

Ordering and shipping details

Category	US1DE3A00001
Discount Schedule	DE3A
GTIN	785901745990
Returnability	Yes
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.70 in (1.78 cm)
Package 1 Width	14.24 in (36.17 cm)
Package 1 Length	17.92 in (45.52 cm)
Package 1 Weight	5.851 lb(US) (2.654 kg)
Unit Type of Package 2	PAL
Number of Units in Package 2	162
Package 2 Height	39.50 in (100.33 cm)
Package 2 Width	40.0000000000 in (101.6 cm)
Package 2 Length	48.0000000000 in (121.92 cm)
Package 2 Weight	946.000 lb(US) (429.098 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------