

Product data sheet

Characteristics

8940SSD4025Y1071

Pump Panel, NEMA Type S, Well Guard, Size 2, 45A, 100 kA SSCR, 25 HP, 60A Class R fuse clip, Motor Logic SSOLR, 440/480 VAC 50/60 Hz coil, NEMA 3R



Main

Product	Well-Guard Control
Type	Class 8940 type SS
Device application	Pumping

Complementary

Control Circuit Type	Common control circuit
Control Circuit Voltage	480 V AC 60 Hz 440 V AC 50 Hz
Line Rated Current	45 A
Number of Poles	3
Horsepower Rating	25 hp 480 V AC, 3 phase
Maximum Voltage Rating	600 V AC
Control Units	Selector switch HAND-OFF-AUTO) Push-button START)
Disconnect Type	Fusible disconnect switch
Associated fuse rating	60 A
Fuse type	R
Thermal overload type	Motor Logic solid state class 10/20
Protection type	Overload Phase loss Phase unbalance
Device mounting	Surface
Electrical connection	Screw terminal
NEMA size	2
Height	39.06 in (992 mm)
Width	15.16 in (385 mm)
Depth	9.69 in (246 mm)

Environment


NEMA Rating	NEMA 3R
Enclosure type	Weatherproof enclosure indoor/outdoor
Product certifications	UL Listed NEMA

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the Schneider Electric group. It is not intended to be used as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Ordering and shipping details

Category	21388 - 8940 NSC,NSD
Discount Schedule	CP1
GTIN	00785901163992
Nbr. of units in pkg.	1
Package weight(Lbs)	71 lb(US) (32.21 kg)
Returnability	Yes
Country of origin	MX

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Not compliant
China RoHS Regulation	 China RoHS Declaration
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------