



Main

| | |
|---------------------|----------------------|
| Product | Surface cover |
| Color | Gray |
| Cover type | Surface cover |
| Type of front plate | Hinged Ventilated |

Complementary

| | |
|-------------------|---------------------|
| Material | Steel |
| Height | 86 in (2184.40 mm) |
| Width | 20 in (508.00 mm) |
| Tightening torque | Cover 10...12 lb.in |

Environment

| | |
|------------------------|--------|
| Enclosure Rating | NEMA 1 |
| Product certifications | CULus |

Ordering and shipping details

| | |
|-----------------------|---------------------------|
| Category | 08352 - NF / NQ TRIMS RTA |
| Discount Schedule | PE1A |
| GTIN | 00785901914655 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 60 lb(US) (27.22 kg) |
| Returnability | Yes |
| Country of origin | US |

Packing Units

| | |
|------------------|-------------------|
| Package 1 Height | 0.15 ft (0.046 m) |
| Package 1 width | 1.84 ft (0.561 m) |
| Package 1 Length | 7.32 ft (2.230 m) |

Offer Sustainability

| | |
|---------------------------|---|
| Sustainable offer status | Green Premium product |
| California proposition 65 | WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |

| | |
|----------------------------|---|
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|