

# Product data sheet

## Characteristics

# UHTRS223A

Individual meter socket, ringless socket, horn bypass, 4 jaws no release, UG, 200 A, up to 600 VAC single phase 3W



### Main

Product or component type	Meter Socket
Meter socket type	Ringless
Hub type	Solid top

### Complementary

Meter socket rated current	200 A
Number of jaws	4 without jaw release
Bypass type	Horn bypass
Phase	1 phase
[Ue] rated operational voltage	600 V AC
Enclosure material	Steel
Box number	2R
Electrical connection	Lugs 0.5" hex
Service feed location	UG
Wiring configuration	3-wire
Device mounting	Surface
AWG gauge	AWG 1/0...350 kcmil 1 aluminium/copper)line AWG 14...AWG 2 1 aluminium/copper)service ground
Height	13.00 in (330.20 mm)
Width	13.00 in (330.20 mm)
Depth	4.94 in (125.48 mm)

### Environment

Product certifications	UL Listed
Enclosure Rating	NEMA 3R

### Ordering and shipping details

Category	00039 - METER SOCKETS & HUBS
Discount Schedule	DE4
GTIN	00785901911685
Nbr. of units in pkg.	1
Package weight(Lbs)	14.23 lb(US) (6.45 kg)
Returnability	Yes
Country of origin	US

## Packing Units

Unit Type of Package 1	PCE
Package 1 Height	6.00 in (15.24 cm)
Package 1 width	13.60 in (34.544 cm)
Package 1 Length	13.60 in (34.544 cm)
Unit Type of Package 2	PAL
Number of Units in Package 2	63
Package 2 Weight	942.00 lb(US) (427.284 kg)
Package 2 Height	47.50 in (120.65 cm)
Package 2 width	42.00 in (106.68 cm)
Package 2 Length	42.00 in (106.68 cm)

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Nickel (Metallic), which is known to the State of California to cause cancer, and Toluene, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
EU RoHS Directive	Under investigation

## Contractual warranty

Warranty	18 months
----------	-----------