



Main

| | |
|---------------------------|-------------------|
| Range of product | Harmony 9001KS |
| Product or component type | Selector switch |
| Device short name | 9001KS |
| Type of operator | maintained |
| Operator profile | Red standard knob |

Complementary

| | |
|-------------------------------|------------------------|
| Bezel material | Chromium plated metal |
| Mounting diameter | 1.18 in (30 mm) |
| Net Weight | 0.54 lb(US) (0.245 kg) |
| Shape of signaling unit head | Round |
| Operator position information | 3 positions |
| Contacts type and composition | Without contact block |
| Mechanical durability | 500000 cycles |
| Device presentation | Basic element |

Environment

| | |
|---------------------------------------|--|
| Protective treatment | TC |
| Ambient air temperature for storage | -40...158 °F (-40...70 °C) |
| Ambient air temperature for operation | -13...158 °F (-25...70 °C) |
| Overvoltage category | Class II conforming to IEC 61140 |
| IP degree of protection | IP66 IEC 60529 |
| NEMA degree of protection | NEMA 1 NEMA 12 NEMA 13 NEMA 2 NEMA 3 NEMA 3R NEMA 4 NEMA 6 |
| Standards | CSA C22.2 No 14 EN/IEC 60947-5-4 JIS C 852 EN/IEC 60947-1 UL 508 EN/IEC 60947-5-1 JIS C 4520 |
| Product certifications | UL 508 NEMA |
| Vibration resistance | 7 gn 2...500 Hz)IEC 60068-2-6 |
| Shock resistance | 50 gn IEC 60068-2-27 |

Ordering and shipping details

| | |
|-----------------------|-------------------------------|
| Category | 21426 - 9001 K (NOT KA,KM,KX) |
| Discount Schedule | CS1 |
| GTIN | 00785901384441 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 0.5 lb(US) (0.23 kg) |
| Returnability | No |
| Country of origin | MX |

Packing Units

| | |
|------------------|----------------------|
| Package 1 Height | 7.62 in (19.355 cm) |
| Package 1 width | 3.00 in (7.620 cm) |
| Package 1 Length | 19.35 in (49.161 cm) |

Offer Sustainability

| | |
|----------------------------|--|
| Sustainable offer status | Green Premium product |
| California proposition 65 | WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |
| WEEE | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|