



Main

| | |
|---------|-------------|
| Range | 9080FB |
| Product | Fuse holder |

Complementary

| | |
|--------------------------------|--|
| Current Rating | 30 A |
| [Ue] rated operational voltage | <= 600 V AC/DC |
| Fuse type | CC |
| Fuse size | 0.4063 x 1.5 in |
| Number of poles | 1 |
| Electrical connection | Pressure wire clamp |
| Wire Gauge | AWG 14...AWG 10 copper or aluminium |
| SCCR | 200 kA UL 512 |
| Product certifications | UL recognized E40747 CCN IZLT2 CSA file 70360 class 6225 01 CE |
| Operating Temperature | -40...257 °F (-40...125 °C) |
| Mounting Type | Surface mount |
| Block Material | Thermoplastic block |
| Wire stripping length | 0.4375 in (11.11 mm) |
| Terminal Tightening Torque | Screw terminals 25 lbf.in (2.82 N.m) AWG 14...AWG 10 copper |
| Height | 3.13 in (79.50 mm) |
| Width | 0.85 in (21.59 mm) |
| Depth | 1.29 in (32.77 mm) |

Ordering and shipping details

| | |
|-----------------------|-----------------------|
| Category | 21701 - 9080 FB |
| Discount Schedule | CP1 |
| GTIN | 00785901097198 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 0.09 lb(US) (0.04 kg) |
| Returnability | Yes |
| Country of origin | US |

Packing Units

| | |
|------------------------|--------------------|
| Unit Type of Package 1 | PCE |
| Package 1 Height | 0.90 in (2.286 cm) |
| Package 1 width | 1.40 in (3.556 cm) |
| Package 1 Length | 3.10 in (7.874 cm) |
| Unit Type of Package 2 | CAR |

| | |
|------------------------------|------------------------|
| Number of Units in Package 2 | 50 |
| Package 2 Weight | 4.58 lb(US) (2.077 kg) |
| Package 2 Height | 3.90 in (9.906 cm) |
| Package 2 width | 6.90 in (17.526 cm) |
| Package 2 Length | 9.70 in (24.638 cm) |

Offer Sustainability

| | |
|----------------------------|---|
| California proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|