

# Product data sheet

## Characteristics

# 8910DPA63V02U1

Contacteur, Definite Purpose, 60A, 3 pole, 30 HP at 575 VAC, 3 phase, 110/120 VAC 50/60 Hz coil, open, UL Listed



### Main

Product or component type	Definite Purpose Contactor
Line Rated Current	60 A
Number of Poles	3P
Pole contact composition	3 NO
Range of product	DPA

### Complementary

Maximum Horse Power Rating	5 Hp 115 V AC, 1 phase 10 Hp 230 V AC, 1 phase 30 Hp 460 V AC, 3 phase 30 Hp 575 V AC, 3 phase 25 hp 230 V AC, 3 phase
Locked rotor rated current	360 A 277 V AC 300 A 460 V AC 240 A 575 V AC
[Ue] rated operational voltage	600 V AC
[Uc] control circuit voltage	120 V AC 60 Hz 110 V AC 50 Hz
Phase	3 phase
Electrical connection	Box lugs

### Environment

Product certifications	UL Listed CSA
------------------------	------------------

### Ordering and shipping details

Category	21346 - 8910 DPA 6_(60 AMP)
Discount Schedule	CP1B
GTIN	00785901167693
Nbr. of units in pkg.	1
Package weight(Lbs)	1.58 lb(US) (0.72 kg)
Returnability	Yes
Country of origin	CN

### Packing Units

Package 1 Height	3.80 in (9.652 cm)
Package 1 width	4.30 in (10.922 cm)
Package 1 Length	2.70 in (6.858 cm)

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>

## Contractual warranty

Warranty	18 months
----------	-----------