



Engineered for comfort, protection and style, Genesis is the number one selling premium eyewear in the market, delivering an incredible range of superior product benefits. Built with MMT— Multi-Material Technology® and a high level of adjustability, Genesis provides workers with extraordinary all-day comfort and raises the bar on compliance.



SAFETY EYEWEAR

Genesis®



**UVE**™  
by Honeywell

## High Performance Protection

- Wrap-around 9-base uni-lens style for uncompromised peripheral vision and superior coverage.
- Available with Dura-streme™ dual coating technology which combines our two best lens coatings — Uvextreme® anti-fog on the interior and Ultra-dura® anti-scratch on the exterior — for 3x longer lens life.\*
- Offers highest available impact protection. Meets ANSI Z87.1-2003 (High Impact) and military V<sub>0</sub> ballistic impact test (protection against impact energies 7x higher than ANSI requirements).
- Certified to meet CSA Z94.3 standards.
- Available in a wide range of lens tints to address the needs of virtually any work environment.

## Superior Comfort & Fit

- Soft elastomer browguard diffuses and deflects impact while providing comfort at all contact points.
- Soft flexible fingers on the nose piece adjust and conform to almost any nasal profile to reduce slippage.
- Adjustable temple length and lens inclination for a customizable fit.

## Product Platform Advantages & Value

- Economical and easy lens replacement system allows for multiple lens tints and extends the life of the eyewear.
- Multiple models in a family offers standardization while offering workers choice.
- Lifetime frame guarantee.



Three position ratchet lens inclination adjusts to complete the fitting system and provides unsurpassed extended wear comfort.



Soft, flexible nose fingers conform to fit a variety of nasal profiles.



A unique ventilation channel, between the frame and lens, vents the eye socket area to deliver an outstanding level of moisture and fog control.



Adjustable temple length enables wearers to custom fit the eyewear to their facial profile.



# Genesis®

All Uvex® lenses offer 99.9% ultra-violet protection.



**Clear** — Ideal for most indoor work applications



**Espresso** — Minimizes strong outdoor sunlight and glare



**Amber** — For low-light applications where enhanced contrast is needed



**SCT-Vermilion** — For indoor applications where contrast is needed, such as inspection



**SCT-Blue** — For applications with high levels of sodium vapor lighting



**Gold Mirror** — Deflects sunlight and glare



**SCT-Reflect 50** — Light mirror coating for varying light conditions



**SCT-Gray** — Minimizes outdoor glare and offers true color recognition



**SCT-Low IR** — When peripheral IR protection is required



**Infra-dura® Welding** — Available in shades 2.0, 3.0 and 5.0 for welding, brazing and cutting



**50% Gray** — Minimizes outdoor sunlight and glare



**Dark Gray** — Minimizes eye fatigue due to outdoor sunlight and glare

FOR MORE INFORMATION, CONTACT:

**Sperian Protection Americas, Inc.**  
900 Douglas Pike  
Smithfield, RI 02917-1874  
(800) 430-5490  
[www.uvex.us](http://www.uvex.us)



by Honeywell

## ORDERING INFORMATION

### EYEWEAR

| ITEM #     | FRAME COLOR                | LENS TINT            | LENS COATING | UPC CODE     |
|------------|----------------------------|----------------------|--------------|--------------|
| S3200      | Black                      | Clear                | Ultra-dura   | 603390087851 |
| S3200D     | Black                      | Clear                | Dura-streme  | 603390122859 |
| S3200-ADV  | Black                      | Clear                | Ultra-dura   | 603390123405 |
| S3200X     | Black                      | Clear                | Uvextreme    | 603390087868 |
| S3200X-ADV | Black                      | Clear                | Uvextreme    | 603390122965 |
| S3201      | Black                      | Espresso             | Ultra-dura   | 603390087875 |
| S3201X     | Black                      | Espresso             | Uvextreme    | 603390087882 |
| S3202      | Black                      | Amber                | Ultra-dura   | 603390087899 |
| S3202X     | Black                      | Amber                | Uvextreme    | 603390102837 |
| S3203      | Black                      | Gold Mirror          | Ultra-dura   | 603390087905 |
| S3204      | Black                      | SCT-Reflect 50       | Ultra-dura   | 603390087912 |
| S3205X     | Black                      | SCT-Gray             | Uvextreme    | 603390095221 |
| S3206      | Black                      | Shade 2.0 Infra-dura | Ultra-dura   | 603390095115 |
| S3207      | Black                      | Shade 3.0 Infra-dura | Ultra-dura   | 603390095122 |
| S3208      | Black                      | Shade 5.0 Infra-dura | Ultra-dura   | 603390095139 |
| S3209      | Black                      | SCT-Low IR           | Ultra-dura   | 603390095146 |
| S3210X     | Black                      | SCT-Vermilion        | Uvextreme    | 603390094989 |
| S3211X     | Black                      | SCT-Blue             | Uvextreme    | 603390095009 |
| S3212X     | Black                      | Dark Gray            | Uvextreme    | 603390100192 |
| S3213X     | Black                      | 50% Gray             | Uvextreme    | 603390106927 |
| S3220      | Earth                      | Clear                | Ultra-dura   | 603390088537 |
| S3220X     | Earth                      | Clear                | Uvextreme    | 603390088544 |
| S3221      | Earth                      | Espresso             | Ultra-dura   | 603390088551 |
| S3221X     | Earth                      | Espresso             | Uvextreme    | 603390088568 |
| S3222      | Earth                      | Amber                | Ultra-dura   | 603390088575 |
| S3223      | Earth                      | Gold Mirror          | Ultra-dura   | 603390088582 |
| S3224      | Earth                      | SCT-Reflect 50       | Ultra-dura   | 603390088599 |
| S3240      | Vapor Blue                 | Clear                | Ultra-dura   | 603390088674 |
| S3240X     | Vapor Blue                 | Clear                | Uvextreme    | 603390088681 |
| S3241      | Vapor Blue                 | Espresso             | Ultra-dura   | 603390088698 |
| S3241X     | Vapor Blue                 | Espresso             | Uvextreme    | 603390088704 |
| S3242      | Vapor Blue                 | Amber                | Ultra-dura   | 603390088711 |
| S3243      | Vapor Blue                 | Gold Mirror          | Ultra-dura   | 603390088728 |
| S3244      | Vapor Blue                 | SCT-Reflect 50       | Ultra-dura   | 603390088735 |
| S3260      | Patriot - Red, White, Blue | Clear                | Ultra-dura   | 603390110979 |
| S3260X     | Patriot - Red, White, Blue | Clear                | Uvextreme    | 603390110986 |
| S3263      | Patriot - Red, White, Blue | Gold Mirror          | Ultra-dura   | 603390111013 |
| S3600      | Mercury Red                | Clear                | Ultra-dura   | 603390122224 |
| S3600X     | Mercury Red                | Clear                | Uvextreme    | 603390122231 |
| S3601      | Mercury Red                | Espresso             | Ultra-dura   | 603390122248 |
| S3601X     | Mercury Red                | Espresso             | Uvextreme    | 603390122255 |
| S3602      | Mercury Red                | Amber                | Ultra-dura   | 603390122262 |
| S3603      | Mercury Red                | Gold Mirror          | Ultra-dura   | 603390122279 |
| S3604      | Mercury Red                | SCT-Reflect 50       | Ultra-dura   | 603390122286 |

### REPLACEMENT LENSES

| ITEM # | LENS TINT            | LENS COATING | UPC CODE     |
|--------|----------------------|--------------|--------------|
| S6900  | Clear                | Ultra-dura   | 603390089343 |
| S6900D | Clear                | Dura-streme  | 603390122927 |
| S6900X | Clear                | Uvextreme    | 603390089350 |
| S6901  | Espresso             | Ultra-dura   | 603390089367 |
| S6901X | Espresso             | Uvextreme    | 603390089374 |
| S6902  | Amber                | Ultra-dura   | 603390089381 |
| S6902X | Amber                | Uvextreme    | 603390102844 |
| S6903  | Gold Mirror          | Ultra-dura   | 603390089398 |
| S6904  | SCT-Reflect 50       | Ultra-dura   | 603390089404 |
| S6905X | SCT-Gray             | Uvextreme    | 603390095030 |
| S6906  | Shade 2.0 Infra-dura | Ultra-dura   | 603390095047 |
| S6907  | Shade 3.0 Infra-dura | Ultra-dura   | 603390095054 |
| S6908  | Shade 5.0 Infra-dura | Ultra-dura   | 603390095061 |
| S6909  | SCT-Low IR           | Ultra-dura   | 603390095153 |
| S6910X | SCT-Vermilion        | Uvextreme    | 603390095160 |
| S6911X | SCT-Blue             | Uvextreme    | 603390095177 |
| S6912X | Dark Gray            | Uvextreme    | 603390100277 |
| S6913X | 50% Gray             | Uvextreme    | 603390106934 |

Packaging Information (Eyewear):  
Ind. Box, 10 / Stocker, 200 / Master Case  
Master Case Weight: 32 pounds  
Master Case Dimensions: 29" x 15" x 24"

Packaging Information (Replacement Lenses):  
Ind. Polybag, 10 / Box, 200 / Master Case  
Master Case Weight: 11 pounds  
Master Case Dimensions: 18" x 13 1/4" x 10"

Uvextreme® anti-fog coating performs under the most extreme conditions and will not wear off after repeated cleanings. It is permanently bonded to the lens and retains anti-scratch, anti-static and UV protection properties. Ultra-dura® hard coat is permanently bonded to the lens and is scratch-resistant and chemical-resistant. Uvex Dura-streme™ lenses combine our two best lens coatings on one lens: Ultra-dura on the exterior and Uvextreme on the interior to provide up to 3x\* more lens life.

\*Comparative lens life test performed using a Bayer Abrasion Test method and may vary between environment and application.

