



Main

Product or component type	Communication card
Range compatibility	Altivar 212
Communication port protocol	LonWorks

Complementary

Electrical connection	Screw terminal NETA, NETB LonWorks transmission/reception data Screw terminal SHLD LonWorks communication shield Screw terminal G/E grounding terminal Spring terminal F programmable logic input Spring terminal R programmable contact input Spring terminal VIB multifunction programmable analog input Spring terminal CC control circuit equipotential Spring terminal P24 power supply output Screw terminal FLA, FLB, FLC multifunction programmable relay output
Input type	Multifunction programmable logic input F < 24 V DC 5 mA sink or source Multifunction programmable contact input R < 24 V DC 5 mA sink or source Multifunction programmable analog input VIB 10 V DC 30 kOhm
Output type	Multifunction programmable relay output FLA, FLB, FLC 250 V AC 1 A 1 Multifunction programmable relay output FLA, FLB, FLC 250 V AC 0.5 A 0.4 Multifunction programmable relay output FLA, FLB, FLC 30 V DC 0.5 A Power supply output P24 24 V DC 50 mA
Electrical connection	Screw/spring terminal block
Net Weight	0.11 lb(US) (0.05 kg)

Ordering and shipping details

Category	22159 - ATV212 OPTIONS
Discount Schedule	CP4D
GTIN	00785901916178
Nbr. of units in pkg.	1
Package weight(Lbs)	0.35 lb(US) (0.16 kg)
Returnability	Yes
Country of origin	CN

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	2.83 in (7.2 cm)
Package 1 width	6.77 in (17.2 cm)
Package 1 Length	9.13 in (23.2 cm)
Unit Type of Package 2	S03
Number of Units in Package 2	7
Package 2 Weight	4.85 lb(US) (2.199 kg)
Package 2 Height	11.81 in (30 cm)

Package 2 width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------