



Main

Product or component type	Industrial Control Transformer
Range of product	Instakits

Complementary

Phase	3 phase 1 phase
Rated power in VA	50 VA
Primary voltage	480 V
Secondary voltage	120 V
Electrical connection	Connector

Environment

Product certifications	CSA UL
------------------------	-----------

Ordering and shipping details

Category	22341 - CONTACTOR,D,K,&F ACCESS
Discount Schedule	I12
GTIN	00785901645627
Nbr. of units in pkg.	1
Package weight(Lbs)	3.34 lb(US) (1.51 kg)
Returnability	Yes
Country of origin	MX

Packing Units

Package 1 Height	6.40 in (16.256 cm)
Package 1 width	6.90 in (17.526 cm)
Package 1 Length	7.90 in (20.066 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------
